


JV666H – GE Profile[™] 36" High Performance Range Hood

Dimensions (in inches)




Model	Α	В	C	D
JV666	4-3/4	35-7/8	20	12

Amp Rating			
120V	2.5		

Installation Information: Before installing, consult installation instructions packed with product for current dimensional data. Light bulb(s) not included.

Specification Revised 5/04 220931



Exhaust outlet connects to 3-1/4" x 10" duct (vertically or horizontally) and 7" round (vertically). Includes rectangular damper and 7" round damper adapter.

Round damper accessory, JXDA22 available at additional cost.

JXHC1 Cord Kit – Allows a receptacle in the cabinet over the range to accommodate either an over-the-range microwave oven or a standard hood.






For answers to your Monogram,[®] GE Profile[™] or GE[®] appliance questions, visit our website at GEAppliances.com or call GE Answer Center[®] service, 800.626.2000.



JV666H – GE Profile[™] 36" High Performance Range Hood



Features and Benefits

- Vented Effectively pulls smoke and vapors out of the cooking area and vents them outside through an external wall.
- Vertical and rear exhaust Provides the option of connecting duct work to either the rear or the top of the hood.
- Four speed fan control Powerful variable speed exhaust system effectively pulls smoke and vapors out of your kitchen.
- Halogen light Provides bright light that illuminates the cooking surface below hood.
- Removable grease filter Durable filters can be removed for easy cleaning and maintenance.
- Round and rectangular ducting Hood is designed to fit either standard round or rectangular duct work.
- Damper included.
- Model JV666HSS Stainless Steel
- Model JV665HWW White on white
- Model JV665HCC Bisque on bisque
- Model JV665HBB Black on black