

Project Name

Location

Prepared By



SATCO S29876

7A19/CL/LED/E26/27K/ES/120V

Notes

[www] 03-22-2021 04:50:59

General

Status	Discontinued
Substitute	S12414
Watts	7
Incandescent Equivalent	60
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	2700
Temperature	Warm White
CRI	83
Lumens	800
Beam Spread	360
Dimmable	Yes - Dimmable
Hours Rated	15000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	50/60 Hz
Dimming Type	Controlled Current
Power Factor	>0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	4.13
MOD	2.38

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2349089
California Status	Non-Compliant
California Compliant Substitute	S29879
Nevada Status	Lawful for sale in Nevada
SDS Sheet	LED_Lamp