

**Low Voltage Linkable & Direct Wire
HXL120/220/320/420**

Project		Fixture Type
Location		Quantity
Approved By	Date	Catalog Number

Features

Xenon undercabinet linkable system offers a compact design and low profile. The housing is 1-5/16" deep by 4" wide, is available in various lengths and includes a high/low switch. The low voltage unit includes 18 watt lamps and is linkable or direct wire. Specular reflector provides maximum light output. Unit is dimmable with high quality low voltage electronic dimmer. Accessories include a 5'3 wire cord and plug, 12" connecting cable and BX and NM cable connector. Full size knock outs are located on the top and back. Quick wire connectors allow for easy hard wire installation. Ends include connector for linkable system up to 560 watts. Applications include kitchens, study areas and displays.



Construction

Housing is die-formed of 22-gauge steel. Separate hingeable service tray allows for easy installation and snaps into position without hardware. Power connections are made inside service tray or with included cord and plug.

Finish

All exposed metal parts are post painted lighting grade white gloss enamel paint or applied oil-rubbed bronze.

Diffuser

Clear tempered textured glass is .100" thick and slides into housing.

Electrical


This unit includes a 75 watt low voltage electronic transformer wired for 120V operation and steps voltage down to 12V for proper lamp operation. High/low switch included.

Lamping

For use with 12 volt 18 watt T5 wedge based xenon lamps included. Lamps are rated for 10,000 hours.

Certification

Fixtures are cULus listed for damp locations and carry a UL rating for undercabinet mounting.



Specifications and dimensions
subject to change without notice.

Ordering Information:

Model No.		Lamps		Dimensions			Mounting
Finish		Qty	Lamp	H	W	L	M
White	HXL118WH	1	18W WEDGE BASE	1-5/16"	4"	9"	5-7/8"
White	HXL218WH	2	18W WEDGE BASE	1-5/16"	4"	12"	9-1/8"
White	HXL318WH	3	18W WEDGE BASE	1-5/16"	4"	18"	15-1/8"
White	HXL418WH	4	18W WEDGE BASE	1-5/16"	4"	24"	21-1/8"
Finish		Qty	Lamp	H	W	L	M
Oil-Rubbed bronze	HXL118RB	1	18W WEDGE BASE	1-5/16"	4"	9"	5-7/8"
Oil-Rubbed bronze	HXL218RB	2	18W WEDGE BASE	1-5/16"	4"	12"	9-1/8"
Oil-Rubbed bronze	HXL318RB	3	18W WEDGE BASE	1-5/16"	4"	18"	15-1/8"
Oil-Rubbed bronze	HXL418RB	4	18W WEDGE BASE	1-5/16"	4"	24"	21-1/8"