

Sheridan Overbed SHB325/332

Features

White linen patterned acrylic front panel provides a soft glow accent to this contemporary three lamp T8 wall mount senior care overbed light. The champagne trim accents identify the graceful shape. The Sheridan "SHB" provides both ambient and task light with a four way pull switch, standard (120 volt only). Top diffuser is clear, and bottom diffuser is frosted white acrylic.

Construction

The ballast/wiring channel is formed from 22-gauge steel and is provided with keyhole mounting slots and wiring access. An internal divider provides separate lamp compartments for controlled up light and down light. The decorative bands are stamped steel and glued to the diffuser. Fixture can mount horizontally only. Power connections can be made in the fixture wiring channel or in a standard junction box (not included).

Finish

All metal parts are finished in plated champagne. Internal housing is finished in a lighting grade baked white enamel.

Diffuser

Diffuser is 0.070" thick matte white acrylic for the down light, clear frosted acrylic for up light, and a white linen pattern acrylic front. Frame mounts to electrical channel with two decorative screws.

Electrical

This unit is wired with two UL listed electronic high power factor instant start ballasts for one up, two down T8 lamps at 120V- 50/60 Hz AC operation. Four position, three circuit pull switch (on up, on down, on both, all off) are standard and located toward the right end. LED nightlight and on/off pull switch is included.

Lamping

For use with (3) T8 linear lamps, not included.

Certification

All fixtures are cULus listed for damp locations.



Options

120-277 universal voltage available without switch and nightlight.

For photometric information, consult factory.

Specifications and dimensions
subject to change without notice.

Project	Fixture Type
Location	Quantity
Approved By	Date
	Catalog Number



Ordering Information:

Model No.	Finish	Lamps		Dimensions			Mounting
		Qty	Type	H	L	D	M
120V							
SHB325ACMV-LA	Champagne	3	F25T8	4-5/8"	44-1/4"	6-1/2"	29-1/8"
SHB332ACMV-LA	Champagne	3	F32T8	4-5/8"	56-1/4"	6-1/2"	41-1/8"