




LTE ANTENNA SPECIFICATIONS

A-CBA-LTE

Burial Antenna


Installation: In the road surface and is typically used for long term installations.
 Type: Wide Band
 Connector: TNC, stainless steel
 Cable length: 10'
 Size: 5" x 2.5" x 0.55" (L x W x H)
 Peak Gain: 2dB
 Frequency range: 700 - 2600MHz



A-EMA-LTE

Enclosure Mount Antenna


Installation: On an enclosure
 Type: Wide Band, Omnidirectional Articulating antenna
 Connector: TNC, nickel plated brass
 Size: 9in x 1.2in x 0.6in (L x W x D)
 Peak Gain: 2.2dB 1710-2700 MHz / 0.5dB 698-960 MHz
 Frequency range: 698-960 MHz/1710-2600 MHz



A-PMA-LTE

Pole Mount Antenna


Installation: On a pole - Mounting kit included
 Type: Wide band, Omnidirectional antenna
 Connector: TNC, nickel plated brass
 Cable length: 15'
 Size: 3.5" tall, 1.5" diameter
 Gain: 3dB
 Frequency: 698-960MHz / 1710-2600 MHz



A-SB-LTE

Blade Antenna


Installation: On the road surface or non-conductive surface; typically used for temporary installations.
 Type: Wide band antenna
 Connector: TNC, nickel plated brass
 Cable length: 10'
 Size: 5.7" x 1" x 0.18" (L x W x H)
 Peak Gain: 1.5dB
 Frequency range: 698-960 MHz / 1710-2600 MHz



A-ETV-LTE

Enclosure Mount Vandal Resistant

Installation: Enclosure Top Vandal Resistant Mount. ¾" mount
 Type: Wide band, Omnidirectional antenna
 Connector: TNC, nickel plated brass
 Size: 3.5" tall, 1.5" diameter
 Gain: 3dB
 Frequency: 698-960MHz / 1710-2600 MHz



© 2018, Telog, A Trimble Company. Telog® is a registered trademark of Telog, A Trimble Company. Specifications within this brochure are subject to change without notification. (2/2018)

U.S.A : TRIMBLE INC.
 3501 Jamboree Road
 Irvine, California 92660
 +1 (949) 892-6120

TELOG (ROCHESTER OFFICE),
 NEW YORK, USA
 830 Canning Parkway
 Victor, New York 14564
 +1 (585) 742-3000

R.O.W : TRIMBLE INC.
 NSC Campus, Mahon,
 Cork Ireland
 +353 21 230 9328

TrimbleWater_ContactUs@trimble.com
 www.trimblewater.com