

## LG REFRIGERATION

# LRSDS2706\_

## 27 cu.ft. Side by Side Refrigerator

Ultra-Large Capacity, 27 cu. ft.

Door-in-Door®

Flat Panel Door Design with Pocket Handles

Dual Ice Maker with Craft Ice™

UVnano™ Smooth Touch Dispenser

CoolGuard™ Interior Panel

Interior LED Lighting

Interior Display Controls

Door Cooling+

Linear Cooling™

Multi-Air Flow System

LG ThinQ® Technology



### Enjoy new ways to control your home with LG smart appliances

**LG ThinQ®**

- Get an alert when kids forget to close the door
- Make more ice while you're at work
- Works with the LG ThinQ® app



## CAPACITY

Refrigerator (cu.ft.)	17.50
Freezer (cu.ft.)	9.60
Total Capacity (cu.ft.)	27.1

## ENERGY

Energy Consumption (kWh/Year)	694
ENERGY STAR® Qualified	ENERGY STAR®

## WATER &amp; ICE SYSTEM

Ice & Water Dispenser	Yes
Dispenser Type	Smooth Touch with UVnano™
Daily Ice Production (lbs)	2.3 lbs
IcePlus™ Production (lbs)	3.0 lbs
Craft Ice™ Daily Ice Production	0.8 lbs
Ice Storage Capacity (lbs)	3.5 lbs
Ice System	SpacePlus®
Dual Ice with Craft Ice™	Yes
Dispenser Light	Yes (Ring Light)
Water Filter	LT1000P

## COOLING

Linear Compressor	Yes
Linear Cooling	Yes
Door Cooling+	Yes
Multi-Air Flow™ System	Yes
Temperature Sensors	4
Refrigerant	R600a: Low Global Warming Potential, Zero Ozone Depletion Potential and More Energy Efficient Refrigerant than R134a

## CONVENIENCE

Display Type	Membrane / White LED
Temperature Controls	Electronic/Digital
Door Alarm	Yes
Child Lock	Yes
Auto Closing Door Hinge	Yes (Cam Hinge Type)
ADA Compliant	Yes
Sabbath Mode	Yes
LoDecibel™ Quiet Operation	Yes

## REFRIGERATOR

No. of Shelves	4
Cantilevered Shelves	Inner Case Supported Type
Shelf Construction	Tempered Glass
CoolGuard™	Yes
Refrigerator Light	Ceiling LED

## REFRIGERATOR DOOR

Door-In-Door®	Yes
No. of Bins	4
Door Bin Construction	1 Piece (Clear)

## FREEZER

Door Type	Side Swing
Drawers/Shelves	Shelves: 4 (Glass) Drawers: 2

Ice Bin / In-Door Ice	Icemaker & Ice Bin in Door
Freezer Light	Ceiling LED
No. of Door Bins/Construction	2 / 1 Piece(Clear)
Freezer Handle	Newly Designed Pocket Handle (Upper and Lower Pockets)

## SMART FEATURES

wi-fi Enabled	Yes
ThinQ®	Yes
SmartDiagnosis™	Yes

## MATERIALS AND FINISHES

Door Type	Flat
Hidden Hinges	Yes
Surface	Smooth
Fingerprint & Smudge Resistant Exterior	Yes
Handles	Newly Designed Pocket Handle (Upper and Lower Pockets)
All Available Colors	PrintProof™ Black Stainless Steel PrintProof™ Stainless Steel
Insulation	Cyclopentane: Low Global Warming Potential, and Zero Ozone Depletion Potential Blowing Agent

## DIMENSIONS/CLEARANCES/WEIGHTS

Width	35 7/8"
Height to Top of Hinge	70 1/2"
Depth with Handles	33 1/2"
Width (Door Open 90° without Handle)	38 7/8"
Case Edge Clearance (Door Fully Open)	28 3/4"
L. Case Edge Clearance (Door Fully Open)	12 1/4"
R. Case Edge Clearance (Door Fully Open)	16 1/2"
Width (Door Open 90° with Handle)	38 7/8"
Width (Door Fully Open without Handle)	64 3/8"
Door Edge Clearance with Handle	3/8"
Door Edge Clearance without Handle	3/8"
Height to Top of Case	68 7/8"
Depth without Door	28 7/8"
Depth without Handles	33 1/2"
Depth (to Hinge Cover)	22 5/8"
Depth (Total with Door Open)	51"
Installation Clearance	Sides 1/8", Top 1", Back 2"
Weight (Unit/Carton)	285.5 lbs / 293.4 lbs
Carton Dimensions (WxHxD)	37 9/16" x 74 5/8" x 34 7/8"

## LIMITED WARRANTY

Parts & Labor	1 Year
Sealed System (Parts & Labor)	5 Years
Compressor (Parts & Labor)	5 Years
Linear Compressor (Parts Only)	6-10 Years

## UPC CODES

LRSDS2706S (PrintProof™ Stainless Steel)	195174007679
LRSDS2706D (PrintProof™ Black Stainless Steel)	195174007655