

# S2246 PAR38 Halogen 39PAR38/HAL/XEN/FL/120V

Lamp Type	Halogen		
Bulb Type	PAR38		
Base Type	E26SK		
Wattage	39		
Color Temperature	2900		
Color Rendering Index CRI	99		



### Lighting Facts Per Bulb

Brightness	530 lumens
Estimated Energy Cost	\$4.70
per year, based on 3 hrs/ Energy cost depends on use.	• .
Average Life	1.4 years
Based on 3 hrs/day	
Light Appearance	e
Warm	Cool
2900 K	
Energy Used	39 watts

#### **Product Information**

#### **Features**

- Energy Saving Halogen
- Bright, Crisp light
- Indoor / Outdoor
- Uniform light output

## **Product Specifications**

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S2246	Halogen	*	120	39	45	PAR38	Medium Skirted
ANSI Base	Lamp Code	Dimmable/Non- Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26SK	39PAR38/HAL/XE	N/FL/12/0e\s	n/a	5 5/16	4 3/4	530	1500
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
2900	Warm White	99	30	15	Box	n/a	Yes