

## BEVERAGE REFRIGERATORS

L3024UI1BPR – 24 Inch Single Zone Beverage Refrigerator, Panel Ready



### FEATURES:

- The soft close Everglide™ shelves and Everglide® hinges help dampen vibration and ensure a smooth cooling and storage experience
- Fully adjustable shelves move up and down vertical tracking to allow for a wide range of heights
- Best-in-class cabinet lighting runs the entire interior length of three sides with versatile LED color options: blue, white and amber
- Commercial grade 304 stainless steel interior and exterior cabinet
- Precision cooling to drive air evenly throughout the interior, preventing unwanted hotspots
- Low-E, double-pane glass door with a layer of argon gas to maximize energy efficiency and deter harmful UV rays

### ADDITIONAL FEATURES:

- Includes three (3) full extension beverage shelves plus one (1) shallow bottom shelf to fully utilize interior space
- The integrated door lock, door ajar alarm and temperature alarm provide an added layer of security
- Vibration-dampening wire shelves with stainless steel decorative fronts are both stylish and functional
- Zero-clearance door hinges allow for a seamless installation with adjacent cabinetry
- Temperature range: 34°F–65°F

**Please note:** Panel ready appliances are designed to utilize custom panels to match your cabinetry. The panel ready finish option does not include the pictured wood paneling.



### WARRANTY:

- Three (3) Years Parts and Labor
- Six (6) Years Sealed System Parts
- See Complete Warranty for Details

### MODEL DETAILS:


Model	Voltage	Door Swing	Finish
L3024UI1BPR-LH	115V	Left Hinge	Panel Ready
L3024UI1BPR-RH	115V	Right Hinge	Panel Ready

### ACCESSORIES:


Model	Description	Finish
HDLPRO	PRO Style Handle for Undercounter Models	Stainless Steel
PL3024UI2WSG28	Replacement Carbon Filter	Gray
PL3024UI1MSG31	Additional Main Beverage Shelf with Trim and Sliding Track	Black

**DIMENSIONS:**

**FRONT**




**SIDE**



Please note: the 23-1/4" depth does not include the depth of the custom panel door

**TOP**



**SPECIFICATIONS:**

<b>Model#</b>	L3024UI1BPR
<b>Capacity (12 oz. Cans)</b>	147
<b>Capacity (Volume)</b>	5.21 cu ft
<b>Product Depth</b>	23-1/4"
<b>Product Height (Min)</b>	34"
<b>Product Width</b>	23-13/16"
<b>Product Weight</b>	156 lbs.
<b>Refrigerant Type</b>	R600a
<b>Temperature Range</b>	34°F–65°F
<b>Power Cord Length</b>	6.5'
<b>Amps</b>	1.5
<b>Electric Supply</b>	115 VAC, 60 Hz



NEMA 5-15P

**INSTALLATION NOTES:**

- The plug requires an additional 2" for clearance; a recessed receptacle may be required for fully recessed installations
- Dimensions in parentheses are in millimeters
- Cutout dimensions are based off a standard 3/4" panel overlay

**CUTOUT DIMENSIONS**

