
aquatherm greenpipe® - pipe SDR 11

Material	:	fusiolen® PP-R
Pipe Series	:	SDR 11 / S 5
In accordance with :		NSF-14, NSF-51, NSF-61, CSA-B137.11, ICC AC 122, ICC ESR 1613, ASTM F 2389, CFIA #A508, ICC PMG-1014, IAPMO, ICC PMG-1014, IAPMO
Form supplied	:	13 ft (4 m) straight lengths and coils
Color	:	green with 4 blue stripes





Pipe			Diameter	Wall thickness	Internal diameter	Water capacity	Weight
Art.-No.	Dimension Nom. I.D. -- O.D.	Packing unit	d (in)	s (in)	d_i (in)	gal/ft	lb/ft
0610208	1/2" -- 20 mm	25	0.79	0.07	0.64	0.017	0.073
0610210	3/4" -- 25 mm	25	0.98	0.09	0.80	0.026	0.111
0610212	1" -- 32 mm	10	1.26	0.11	1.03	0.043	0.178
0610214	1.25" -- 40 mm	10	1.57	0.15	1.28	0.067	0.279
0610216	1.5" -- 50 mm	5	1.97	0.18	1.61	0.105	0.433
0610218	2" -- 63 mm	5	2.48	0.23	2.02	0.167	0.682
0610220	2.5" -- 75 mm	5	2.95	0.27	2.42	0.237	0.951
0610222	3" -- 90 mm	3	3.54	0.32	2.90	0.343	1.374
0610224	3.5" -- 110 mm	2	4.33	0.39	3.54	0.512	2.107
0610226	4" -- 125 mm	1	4.92	0.45	4.02	0.661	2.639
0610230	6" -- 160 mm	1	6.30	0.57	5.15	1.082	4.311
0610234	8" -- 200 mm	1	7.87	0.72	6.44	1.692	6.713
0610238	10" -- 250 mm	1	9.84	0.89	8.06	2.646	10.442
The following items are supplied in coils:							
0610308	1/2" -- 20 mm	328 ft	0.79	0.07	0.64	0.017	0.726
0610310	3/4" -- 25 mm	328 ft	0.98	0.09	0.80	0.026	0.106
0610312	1" -- 32 mm	164 ft	1.26	0.11	1.03	0.043	0.173