



- G1635** Emergency Shower, Vertically Mounted, Plastic Shower Head
- G1635SSH** Emergency Shower, Vertically Mounted, Stainless Steel Shower Head

Application: Emergency shower for vertical mounting.

Shower Head: 10" diameter with 20 GPM flow control. Shower head is orange ABS plastic (G1635) or stainless steel (G1635SSH).

Valve: 1" IPS chrome plated brass stay-open ball valve. Valve is US-made with chrome plated brass ball and PTFE seals. Furnished with stainless steel actuating arm and 29" stainless steel pull rod.

Supply: 1" NPT female inlet.

Sign: ANSI-compliant identification sign.


Available Options

- G6040** Thermostatic mixing valve precisely blends hot and cold water to deliver tepid water as required by ANSI Z358.1-2014. Refer to "Thermostatic Mixing Valves" section for complete technical and product selection information.
- GRN** Safety green ABS plastic shower head.
- YEL** Safety yellow ABS plastic shower head.
- AP280-200** Electric flashing light and alarm horn unit for mounting on wall or vertical pipe. Light illuminates and horn sounds when shower is activated. Furnished complete with flow switch and mounting hardware.






- **G1635** Emergency Shower, Vertically Mounted, Plastic Shower Head
- **G1635SSH** Emergency Shower, Vertically Mounted, Stainless Steel Shower Head



Rev. 032918

THIS SPACE FOR ARCHITECT/ENGINEER APPROVAL

Sign Included



Due to continuing product improvement, the information contained in this document is subject to change without notice. All dimensions are $\pm 1/4"$ (6mm). rev. 062018

