



G1643 Emergency Shower, Horizontally Mounted, Plastic Shower Head
G1643SSH Emergency Shower, Horizontally Mounted, Stainless Steel Shower Head

Application: Emergency shower for horizontal mounting. **Shower Head:** 10" diameter. Shower head is orange ABS plastic (G1643) or stainless steel (G1643SSH).

Valve: 1" IPS chrome plated brass stay-open ball valve. Valve is US-made with chrome plated brass ball and Teflon® seals. Furnished with stainless steel actuating arm and 29" stainless steel pull rod.

Pipe and Fittings: 1" IPS galvanized steel nipple with orange ABS plastic elbow (G1643) or galvanized street elbow (G1643SSH).

Supply: 1" NPT female inlet.

Sign: ANSI-compliant identification sign.

Available Options

PCC All-polished chrome plated brass construction.
GRN Safety green ABS plastic shower head.
☐ YEL Safety yellow ABS plastic shower head.
PCH Polished chrome plated cast brass shower head.
FC20 Regulates shower flow rate to 20 GPM.
SC Self-closing ball valve. Note: Emergency showers with self-closing valves do not comply with ANSI Z358.1-2014.



Flashing light and horn serve to summon assistance when shower is activated.

TMV G3800LF thermostatic mixing valve precisely blends hot and cold water to deliver warm (tepid) water as required by ANSI Z358.1-2014. Refer to "Tempering Units" section for complete technical and product selection information.


AP250-015 MODESTY CURTAIN

Modesty curtain for horizontal shower installation.





- ☐ **G1643** Emergency Shower, Horizontally Mounted, Plastic Shower Head
- ☐ **G1643SSH** Emergency Shower, Horizontally Mounted, Stainless Steel Shower Head



THIS SPACE FOR ARCHITECT/ENGINEER APPROVAL

Due to continuing product improvement, the information contained in this document is subject to change without notice. All dimensions are \pm 1/4" (6mm). rev. o61 rev. 0615

UPC listed 8116. ETL listed 101496. Units have been tested to and comply with ANSI Z358.1-2014.