Freestanding Ranges



Signature Features

Ready-Select® Controls

Select options or control cooking temperature with our easy-to-use controls.

One-Touch Self Clean

Start the self-cleaning cycle with just the touch of a button.

Large Capacity

Our large capacity oven gives you room to cook more at once.

Even Baking Technology

Our latest technology ensures even baking every time.



30" Electric

Product Dimensions

Height (Max.)	47-1/2"
Width	29-7/8″
Depth (Including Handle)	28-1/2"

More Easy-To-Use Features

Store-More™ Storage Drawer Our convenient drawer gives you extra storage space in your kitchen.

Quick Clean For a quick, light oven cleaning.

Extra-Large Window Our extra-large oven window lets you easily see what's inside.

Delay Start Baking Option

Delay Clean Set the oven to begin cleaning on your schedule.

Hi/Lo Broil Option Offers two-position broiling and variable temperature control for more control.

Auto Shut-Off As an extra safety measure, the oven will automatically shut off after 12 hours.

Timed Cook Option

Bright Lighting Our bright lighting makes it easy to see what's inside.

Attractive Stainless Steel Exterior¹

Available in:



Black (B)


Elements	Size	Watts
Right Front	9″	2,500
Right Rear	6″	1,200
Left Front	9″	2,500
Left Rear	6″	1,200

'Select model only.

Freestanding Ranges

FFEF3017L S/W/B **30" Electric**

Features	
Oven Control/Timing System	Ready-Select* Controls
Surface Type	Black Ceramic Glass
Window	Extra-Large
Exterior Door Finish	Stainless Steel (S), Color-Coordinated (W/B)
Handle Design	Black (S), Color-Coordinated (W/B)
Exterior Finish (Side Panels)	Black (S), Color-Coordinated (W/B)
Convection System	
Oven Cleaning System	Self Clean
Drawer Functionality	Storage
Oven Controls	
Bake	Yes
Broil	Low and High
Add-a-Minute	
Delay Bake	Yes
Self-Clean	Yes
Quick Clean Option	Yes
Delay Clean	Yes
Kitchen Timer	Yes
Timed Cook Option	Yes
Auto Oven Shut-Off	12 Hours
Cooktop Features	
Right Front Element (Watts)	9″ - 2,500
Right Rear Element (Watts)	6" - 1,200
Left Front Element (Watts)	9″ - 2,500
Left Rear Element (Watts)	6" - 1,200
Center Element (Watts)	
Hot Surface Indicator Light	
Coil Cooktop/Drip Bowls	
Oven Features	
Capacity (Cu.Ft.)	5.3
Oven Light	1
Hidden Bake Element	
Rack Configuration	2 Standard
Even Baking System	Yes
Broiling System	Vari-Broil™ Hi/Lo
Bake Element/Broil Element (Watts)	2,600/3,000
Specifications	
Oven Interior (H x W x D)	21" x 24-3/8" x 19-1/8"
Power Supply Connection Location	Middle Bottom Rear
Voltage Rating	240V/208V/60Hz
Connected Load (kW Rating) @ 240/208 Volts	12.5/9.5
Minimum Circuit Required (Amps)	40
Shipping Weight (Approx.)	140 Lbs.



NOTE: For planning purposes only. Always consult local and national electric codes. Refer to Product Installation Guide for detailed installation instructions on the web at frigidaire.com.


Product Dimensions		Cutout Dimensions	
A-Height (Max.)	47-1/2"	Height (Standard)	36″
B-Width	29-7/8″	Width (Min.)	30"
C-Depth (Including Handle)	28-1/2"	Depth (Min.)	24"
Depth with Door Open 90 $^\circ$	48-3/8"		

Accessories information available on the web at **frigidaire.com**

ŰĽ

Freestanding Ranges

FFEF3017L S/W/B 30" Electric



297/8"

Freestanding Range Specifications

- Product Shipping Weight (approx.) 140 Lbs.
- Single phase 3- or 4-wire cable, 120/240 or 120/208 Volt, 60 Hertz, fused on both sides of line with ground
- Connected Load (kW Rating) @ 240/208 Volts = 12.5/9.5kW
- Recommended Circuit Breaker 40 Amps
- Always consult local and national electric codes.
- Make sure wall coverings around range can withstand heat generated by range.
- Floor beneath range MUST be solid and level.
- Overhead cabinetry should not exceed a 13" maximum depth.
- Absolute minimum horizontal distance between overhead cabinets installed to either side of appliance must be no less than maximum width of appliance.
- Range can be installed flush to wall with O" minimum rear clearance.
- Minimum 1" clearance required from edge of rangetop to nearest combustible wall on either side of range above 36" height.


- Allow 30" minimum clearance between top of cooking surface and bottom of unprotected wood or metal overhead cabinet; or 24 minimum clearance when bottom of wood or metal overhead cabinet is protected by not less than 1/4" flame retardant millbard covered with not less than No. 28 MSG sheet steel, 0.015" stainless steel, 0.024" aluminum or 0.020" copper.
- To reduce risk of fire when using overhead cabinetry, install range hood that projects horizontally a recommended minimum of 5" beyond bottom of cabinets.
- Follow all dimension requirements provided to prevent property damage, potential fire hazard, and incorrect countertop and cabinet cuts.
- Note: For planning purposes only. Refer to Product Installation Guide on the web at frigidaire.com for detailed instructions.



FRIGIDAIRE USA • 10200 David Taylor Drive • Charlotte, NC 28262 • 1-800-FRIGIDAIRE • frigidaire.com CANADA • 5855 Terry Fox Way • Mississauga, ON L5V 3E4 • 1-800-265-8352 • frigidaire.ca FFEF3017L 10/11

General Installation Guidelines

with Side-by-Side Refrigerator




Use these dimensions and clearance instructions for planning purposes only. For detailed installation instructions, refer to installation guide, packed with product, or on the web at frigidaire.com.

FRIGIDAIRE

USA • 10200 David Taylor Drive • Charlotte, NC 28262 • 1-800-FRIGIDAIRE • frigidaire.com CANADA • 5855 Terry Fox Way • Mississauga, ON L5V 3E4 • 1-800-265-8352 • frigidaire.ca

General Installation Guidelines



Use these dimensions and clearance instructions for planning purposes only. For detailed installation instructions, refer to installation guide, packed with product, or on the web at frigidaire.com.

FRIGIDAIRE

USA • 10200 David Taylor Drive • Charlotte, NC 28262 • 1-800-FRIGIDAIRE • frigidaire.com CANADA • 5855 Terry Fox Way • Mississauga, ON L5V 3E4 • 1-800-265-8352 • frigidaire.ca