

**Type K – Soft Coils**

<b>COPPER TUBE IN SOFT LENGTHS</b>					
<b>Part #</b>	<b>Nom. Dia.</b>	<b>O.D. Dia.</b>	<b>Length (Ft.)</b>	<b>Weight / Coil</b>	<b>Master Quantity</b>
KS02060	1/4"	3/8"	60'	8.7	1
KS03060	3/8"	1/2"	60'	16.14	1
KS04060	1/2"	5/8"	60'	20.58	1
KS06060	3/4"	7/8"	60'	38.46	1
KS10060	1"	1-1/8"	60'	50.34	1

**Type L – Soft Coils**

<b>COPPER TUBE IN SOFT LENGTHS</b>					
<b>Part #</b>	<b>Nom. Dia.</b>	<b>O.D. Dia.</b>	<b>Length (Ft.)</b>	<b>Weight / Coil</b>	<b>Master Quantity</b>
LSC2005P	1/4"	3/8"	5'	0.63	5
LSC2010P	1/4"	3/8"	10'	1.26	5
LSC2020P	1/4"	3/8"	20'	2.52	5
LSC2030P	1/4"	3/8"	30'	3.78	5
LS02060	1/4"	3/8"	60'	7.56	1
LSC3010P	3/8"	1/2"	10'	1.98	5
LSC3020P	3/8"	1/2"	20'	3.96	5
LS03060	3/8"	1/2"	60'	11.88	1
LSC4010P	1/2"	5/8"	10'	2.85	5
LSC4020P	1/2"	5/8"	20'	5.7	5
LSC4030PS	1/2"	5/8"	30'	8.55	1
LS04060	1/2"	5/8"	60'	17.1	1
LSC6030PS	3/4"	7/8"	30'	13.65	1
LS06060	3/4"	7/8"	60'	27.3	1
LS10060	1"	1-1/8"	60'	39.3	1

**Dehydrated Refrigeration Coils (O.D. Diameters)**

<b>COPPER TUBE IN SOFT LENGTHS</b>				
<b>Part #</b>	<b>O.D. Dia.</b>	<b>Length (Ft.)</b>	<b>Weight / Coil</b>	<b>Carton Quantity</b>
D04010P	1/4"	10'	0.804	5
D04020P	1/4"	20'	1.608	5
D04050P	1/4"	50'	4.02	10
D06010P	3/8"	10'	1.34	5
D06020P	3/8"	20'	2.68	5
D06050P	3/8"	50'	6.7	1
D08050P	1/2"	50'	9.1	1
D10050P	5/8"	50'	12.55	1
D12050P	3/4"	50'	15.25	1
D14050P	7/8"	50'	22.75	1