


QB2W

Twin 75 watt Quartz Bullet floods come pre-assembled and pre-wired on C103 Mounting plate. Lamps supplied.

Color: White

Weight: 2.1 lbs



Lamp Info

Type: T-4
Watts: 75W
Shape/Size: N/A
Base: N/A
ANSI: N/A
Hours: 1,500
Lamp Lumens: 1,500
Efficacy: 20 LPW

Ballast Info

Type: 0
120V: N/A
208V: 0
240V: N/A
277V: N/A
Input Watts: 75W
Efficiency: 100%

Technical Specifications

UL Listing:

Suitable for wet locations. Suitable for mounting within 1.2m (4ft) of the ground

Housing:

Precision die cast aluminum, 1/2" NPS threaded arm with locking swivel and EZ Grip lock nut fits all standard mounting covers.

Lens Gasket:

High temperature silicone gasket stays in place during relamping

Reflector:

Semi-specular anodized aluminum

Sockets:

Porcelain bi-pin GY 8 base with gold plated contacts and 250°deg; C socket wires

Lens:

Thick, tempered glass

Finish:

Chip and fade resistant polyester powder coating

Replacement Lamps:

Installation:

Twin 75w Flood Kit pre-assembled on C103 plate for easy installation

Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws

:

