


STL110W

STEALTH Sensor with 110° view. Double Look Down lens, surge protection, LED detection indicator and Color Matched Lens.

Color: White

Weight: 1.0 lbs



Technical Specifications

UL Listing:

Suitable for wet locations

Power Consumption:

1 watt

Time Adjustment:

5 seconds to 12 minutes

Surge Protection:

Withstands up to 6000 volts

Wide Sensitivity Control:

Adjustable from 100% to 30%

Temperature Compensation:

Sensitivity adjusts automatically for consistent detection in hot and cold ambient temperatures

Wall Switch Manual Override:

Two flip logic prevents activation by momentary power outages. Override resets to auto at dawn. No extra wiring needed

LED Detection Indicator:

Shows when sensor is detecting in daytime and glows red at night for "on-guard" deterrence

Advanced Detection Logic:

Minimizes false triggers

Color Matched Lens:

Dark lens with bronze units, white lens with white units

RF Immunity:

Circuits fully shielded for maximum radio frequency immunity

Horizontal Lock, No-tool Joints:

Keeps sensing pattern level for fast, error-free installation

Photoelectric Control:

Deactivates lights during daylight. Fully adjustable for 24 hour operation or custom applications

Floodlights:

Precision die cast aluminum. 1/2" NPS threaded arm with serrated locking swivel fits all standard mounting boxes and covers

Voltage:

120 Volts AC 60 Hertz

Detection:

110° view

Switching Capacity:

1000 watts incandescent @ 120 volts, 8 amps

Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.

Warranty:

10 year sensor warranty