Specifications

PFXC9011 TECOPA SINGLE HANDLE KITCHEN FAUCET WITH PULL DOWN SPRAY



Product Features

- Ceramic disc cartridge
- · Metal lever handle
- 2 function sprayhead with pause
- · Single hole or 3-hole sink installation with included optional deck plate
- PFXC9011CP/BN Max. flow rate: 1.8 gpm (6.8L/min) at 60 psi
- PFXC9011LFBN Max. flow rate: 1.0 gpm (3.7L/min) at 60 psi
- Lifetime limited warranty
- Meets ASME : A112.18.1
- NSF 61 compliant
- cUPC/IAPMO listed
- ADA compliant

Model Numbers

PFXC9011CP (1.8 gpm)	Chi
PFXC9011ZBN(1.8 gpm)	PVI
PFXC9011LFZBN (1.0 gpm)	PVI


Chrome PVD brushed nickel PVD brushed nickel

Available Parts

OBPF63538502*Sprayhead(1.8gpm)**PFXC9011SPRY***Sprayhead(1.0gpm)

Note: 1.0 gpm sprayheads available as optional low flow sprayheads for faucet PFXC9011CP/ZBN. PFXC9011LFZBN is available as a full faucet with 1.0 gpm flow rate. PFX9011CP

Product Specifications



* All measurements are nominal. Please verify before actual installation.

Warranty and Codes

This product comes complete with installation, operating, care and maintenance instructions. This PROFLO faucet carries a limited lifetime warranty when installed in residential applications. The warranty is five years in commercial applications. This product meets ASME: A112.18.1. *Compliant with lead content requirements of US Senate Bill S.3874*



FERGUSON.COM/PROFLO