

## Specifications

# PFWSC8840 - ORRS Two Handle Lavatory Faucet



### Product Features

- Ceramic disc cartridges
- Metal lever handle
- Requires 3-hole sink with 4" on-center
- With metal pop-up
- 100% factory pressure tested
- Max. flow rate: 1.2 gpm (4.5 L/min) at 60 psi
- EPA WaterSense approved
- cUPC/IAPMO listed
- ADA compliant


### Model Numbers

PFWSC8840CP	Chrome
PFWSC8840ZBN	PVD brushed nickel
PFWSC8840MB	Matte black



PFWSC8840CP

### Product Specifications



\*All measurements are nominal. Please verify before actual installation.

### Warranty and Codes

This product comes complete with installation, operating, care and maintenance instructions. This PROFLO faucet carries a limited lifetime warranty when installed in residential applications. The warranty is five years in commercial applications. Compliant with lead content requirements of California AB 1953 and Vermont S.152.

