



# 4" LOW VOLTAGE UNIVERSAL TC HOUSING

50W MR16  
TC44

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact/Phone: \_\_\_\_\_

## PRODUCT DESCRIPTION

TC Housing design for use in non-insulated areas • If installed where insulation is present, the insulation must be pulled back 3" from all sides of the TC housing.

## PRODUCT SPECIFICATIONS

**Lamp** One 12V, 50W MR16 lamp.

**Socket** Ceramic bi-pin socket with aluminum heat shield.

**Trims** Trim selection shown on reverse.

**Transformer** 120V to 12V 50VA thermally protected magnetic transformer mounted to junction box.

**Dimming** May be dimmed using dimmers specifically designed for low voltage magnetic transformers; consult factory or dimmer manufacturer for additional information.

**Labels** U.L. listed for through-branch wiring, damp locations and IP • Product thermally protected against improper use of lamps or insulation • Union made • UL Listed/CSA certified • Trim No. 441, 4401, 4402 and 4481 are wet location approved for covered ceiling applications.

**Testing** All reports are based on published industry procedures; field performance may differ from laboratory performance.

Product specifications subject to change without notice.

## INSTALLATION



**Real Nail 3 Bar Hangers** Telescoping, patent-pending Real Nail 3 system permits quick placement of housing anywhere within 24" O.C. joists or suspended ceilings • Integral T-bar notch and clip secures housing in suspended ceiling grid – no accessory clips required • 24" expansion stop allows quick placement of fixture in standard grid spacing • Bars scored in two locations for fast, clean breaking, allowing housing installation in tight applications • Bars captive to mounting frame • Edge-mounted for extra strength • Captive bugle-headed ring shank nail for quick one-step installation and easy removal with claw hammer for fixture relocation • Quick-Loc slot and oversized locking set screw lock fixture in position • Bar hanger foot contoured to align to bottom of construction joist • Alternate mounting holes included.

**Junction Box** Pre-wired junction box provided with (5) 1/2" and (1) 3/4" knockouts, (4) Non-metallic sheathed cable connectors and ground wire, U.L. listed/CSA certified for through-branch wiring, maximum 8 No. 12 AWG 90° C branch circuit conductors (4 in, 4 out) • Junction box provided with removable access plates • Knockouts equipped with pryout slots.

**Mounting Frame** 22-gauge die-formed galvanized steel mounting frame • 10 1/4" L x 5 3/4" W, (excluding bar hangers) • Rough-in section (junction box, mounting frame, housing and bar hangers) fully assembled for ease of installation.

**Housing** TC housing, 22-gauge galvanized steel • Housing is vertically adjustable to accommodate up to a 1 1/4" ceiling thickness.

## DIMENSIONS



4 1/2" CEILING CUTOUT

## ACCESSORIES

Catalog No.	Description
4TSA	Torsion Spring Adapter (for original style housing)

To order, specify catalog number.



















## PRODUCT CODES

Catalog Number	Input Voltage	Lamp Rating (max.)
TC44	120V	12V 50W MR16

# 4" LOW VOLTAGE UNIVERSAL TC HOUSING

50W MR16  
TC44

## TRIMS

Cat. No.	Description	Cat. No.	Description
 <b>442C-WH</b> <b>442G-WH</b> <b>442B-WH</b> <b>442HZ-WH</b> <b>442WHZ-WH</b>	Deep Cone Downlight - Clear Alzak® Deep Cone Downlight - Gold Alzak® Deep Cone Downlight - Black Alzak® Deep Cone Downlight - Haze Deep Cone Downlight - Wheat Haze	 <b>441W-WH ♦</b> <b>441W-SC ♦</b> <b>441W-ABZ ♦</b>	Adjustable Shower Trim, frosted lens with clear center 35° Vertical Adjustment
 <b>443B-WH</b>	Pinhole with Black Baffle Downlight	 <b>446-WH</b>	Scoop Adjustable 50° Vertical Adjustment
 <b>440-WH</b> <b>440-BL</b> <b>440-SC</b> <b>440-ABZ</b>	Flush Gimbal Ring Flush Gimbal Ring Flush Gimbal Ring Flush Gimbal Ring 40° Vertical Adjustment	 <b>4401-WH ♦</b> <b>4401-SC ♦</b> <b>4401-ABZ ♦</b>	Beveled Dome Shower Beveled Dome Shower Beveled Dome Shower
 <b>444B-WH</b> <b>444B-SC</b> <b>444B-ABZ</b> <b>444B-BL</b> <b>444W-WH</b>	Downlight or Adjustable with Black Baffle Downlight or Adjustable with Black Baffle Downlight or Adjustable with Black Baffle Downlight or Adjustable with Black Baffle Downlight or Adjustable with White Baffle 35° Vertical Adjustment	 <b>4402-WH ♦</b> <b>4402-SC ♦</b> <b>4402-ABZ ♦</b>	Beveled Adjustable Shower Beveled Adjustable Shower Beveled Adjustable Shower
 <b>445-WH</b>	Slot Aperture Downlight or Adjustable 50° Vertical Adjustment	 <b>4403FROST-WH</b> <b>4403FROST-SC</b>	Beveled Adjustable Cylinder Beveled Adjustable Cylinder
 <b>447C-WH</b> <b>447G-WH</b> <b>447B-WH</b> <b>447PT-SC</b> <b>447HZ-WH</b> <b>447WHZ-WH</b> <b>447WHZ-ABZ</b>	Downlight or Adjustable - Clear Alzak® Downlight or Adjustable - Gold Alzak® Downlight or Adjustable - Black Alzak® Downlight or Adjustable - Pewter Alzak® Downlight or Adjustable - Haze Downlight or Adjustable - Wheat Haze Downlight or Adjustable - Wheat Haze 35° Vertical Adjustment	 <b>4404HZ-SC</b> <b>4404WHZ-ABZ</b>	Beveled Adjustable Cone Beveled Adjustable Cone
 <b>448-WH</b> <b>448-SC</b>	Eyeball with Black Baffle Eyeball with Black Baffle 35° Vertical Adjustment	 <b>4450MESH-SC</b>	Cylinder
 <b>449-WH</b> <b>449-BL</b> <b>449-SC</b> <b>449-ABZ</b>	75° Vertical Aiming Adjustment	 <b>4480FROST</b>	Solid Glass Collar (torsion spring attachment)
 <b>XR16101WH</b> <b>XR16101BL</b> <b>XR16101GP</b> <b>XR16101SL</b>	AVIO Square Gimbal Ring AVIO Square Gimbal Ring AVIO Square Gimbal Ring AVIO Square Gimbal Ring	 <b>4481CLEAR ♦</b>	All Glass Shower (torsion spring attachment)

Note: Lamps may be dimmed. Use dimmers specifically designed for low voltage magnetic transformers; consult factory or dimmer manufacturer for additional information.

Trim Size: 5" O.D.

**Trim Finish:** ABZ - Classic Aged Bronze, BL - Black, GP - Graphite, PW - Plastic White (Polycarbonate material shower trim), SC - Satin Chrome, SL - Silver, WH - White.  
Alzak is a registered trademark of Alcoa Corp.

♦ UL Listed for use in wet location.



1300 S. Wolf Road • Des Plaines, IL 60018 • Phone (847) 827-9880 • Fax (847) 827-2925  
220 Chrysler Drive • Brampton, Ontario • Canada L6S 6B6 • Phone (905) 792-7335 • Fax (905) 792-0064  
Visit us at [www.junolightinggroup.com](http://www.junolightinggroup.com)

Printed in U.S.A. ©2008 Juno Lighting, LLC.