




Serie MINI BALL VALVE

Articolo **383M**





**RUBINETTERIE
BRESCIANE**

Nickel plated brass ball valve mini series, standard port from 1/8" to 3/4".

- Pressure rating 450 psi.
- Temperature range -4°F to +330°F.
- Blow out proof stem, chrome plated brass ball.
- P.T.F.E seats and viton seal.
- 100% electronically tested in the open and closed position at 80 psi.
- Not to be used for drinking water.
- Valve to be used in fully open or fully closed position.
- ANSI B1.20.1 connections.

383M: MNPT X FNPT THREADED.

MEETS THE DESIGN CRITERIA OF
MSS_SP_110



N Pos	PART NAME	MATERIAL	N PCS
1	BODY	BRASS C38000	1
2	RATAINING BUSH	BRASS C38000	1
3	BALL	BRASS C38000	1
4	BALL SEAT	P.T.F.E	1
5	BALL SEAT	P.T.F.E	1
6	O-RING	FKM (Viton®)	1
7	SCREW	Steel DD11	1
8	STEM	BRASS C38500	1
9	HANDLE	GLASS REINFORCED NYLON	1

SIZE	ØP	CH	I	h	L	R	CV	psi	Weight Lbs
1/8"	0.31	0.83	0.27	1.16	1.61	0.81	4.97	450	0.19
1/4"	0.31	0.83	0.39	1.16	1.69	0.81	4.97	450	0.18
3/8"	0.31	0.83	0.41	1.16	1.69	0.81	3.12	450	0.17
1/2"	0.39	0.98	0.54	1.24	2.17	0.81	6.24	450	0.33
3/4"	0.47	1.18	0.56	1.32	2.36	0.81	8.44	450	0.46

WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.p65warnings.ca.gov.