
EZT HOME V2.0 ATTACHMENT FEATURES & SPECIFICATIONS



FEATURES AND SPECIFICATIONS:

- ATTACHES TO MOST STANDARD CURB KEYS (OLD, NEW, HOMEMADE, LONG AND SHORT)
 EZT ATTACHMENT WORKS IN 2" DIA PORTS AND LARGER.
- PRECISION MACHINED HIGH STRENGTH ALUMINUM ATTACHMENT BRACKET AND CLAMPS.
 - 1 15/16" MAX DIA WORKS IN 2" PORTS

 - 2 A SHAFT CLAMP: CLAMPS AND ALIGNS TO CURB KEY SHAFT WITH "SAFETY KEEPER" FEATURE.
 2 B TOOL END CLAMP: CLAMPS TO CURB KEY TOOL END ENABLING TRANSMISSION OF TORQUE.
 - (2) C SHAFT MOUNT BRACKET: ADAPTS TO LARGE VARIETY OF STANDARD CURB KEYS.
- (3) Stainless Steel Hardware, needs only one tool to assemble (5/32" allen wrench)
- PRECISION MACHINED HIGH STRENGTH ALUMNINUM PATENT-PENDING "EZT TOOL HOUSING" FEATURES:
 - MIN PORT SIZE: 2" PORT (1 15/16" MAX TOOL DIA)
 - TORQUE: TRANSMITS 80 TO 200 FT-LBS (SEE TORQUE SPEC DETAIL)
 - ANTI STICTION FEATURE: PREVENTS "STICTION" DUE TO AIR, WATER AND MUD IN 2" PORTS
- EXTENDED HARDENED STAINLESS STEEL PINS AND STAINLESS STEEL SPRINGS (NOT SHOWN) 1. HIGH STRENGTH TRANSMITS TORQUES UP TO 200 FOOT-POUNDS
 - 2. HIGH COMPLIANCE WILL CONFORM AROUND MOST COMMON WATER VALVE KNOBS INCLUDING:
 - STOP AND WASTE
 - QUARTER ANGLE
 - CORP STOPS
 - CROSSED KNOB
 - BROKEN KNOBS
 - METER LID PENTA NUTS
 - 3. EXTENDED PINS ENABLES EZT TOOL HEAD TO ENGAGE VALVE KNOBS BY EDGE DRAMATACILLY EXTENDING RANGE OF ENGAGEMENT, REDUCTION OF TRAIL AND ERROR IN DIFFICULT INSTALLATIONS AND THUS "SAVES THE FISHING FOR THE LAKE"


EZT TORQUE SPECIFCATION/RATING

THE TOOL TORQUE RATING VARIES FROM 80 TO 200 FOOT-POUNDS DEPENDING ON TOOL ENGAGEMENT WITH THE VALVE KNOB. THE ILLUSTRATIONS BELOW SHOW THE RANGE OF EXPECTED TOOL TO VALVE KNOB ENGAGEMENT AND CORESPONDING TORQUE RATING.

CENTER ENGAGEMENT: 200 FT-LBS TOOL ENGAGES VALVE KNOB THROUGH CENTER MAXIMIZING PINS ENGAGED.



MAX RATING: 200 FT-LBS



EDGE ENGAGEMENT: 80 FT-LBS TOOL ENGAGES VALVE KNOB EDGE MINIMIZING PINS ENGAGED.



MAX RATING: 80 FT-LBS

