



LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		

Dayton Pendant DYP Series

Features

Transitional shaded pendant is available in 24" and 30" diameters. Pendant has a satin nickel finish and includes a hard backed cream linen shade with white acrylic bottom diffuser; open top and center lock up. Pendant is cable mounted and fully adjustable to 4' long. Fixture mounts to a standard junction box (not included).

Construction

Gear plate is die-formed of 20-gauge steel. Trim ring is 22-gauge steel and finial is die cast aluminum. Power supply connections must be made inside a junction box (not included).

Finish

Gear plate is finished in lighting grade white baked gloss enamel paint. Trim ring and finial have an applied satin nickel finish with a clear lacquer topcoat.

Diffuser

Diffuser consists of 24" or 30" hard backed cream linen shade and .090" thick matte white acrylic bottom.

Electrical

This unit can be ordered in one of two options: a UL listed electronic high power factor instant start ballast for 120-277V 50/60 Hz AC operation or line voltage socket for GU24 self-ballast dimmable lamps.

Lamping

Universal ballast lamping is ballasted for 4/18 watt for the 24" diameter and 6/18 watt for the 30" diameter; lamps are supplied by others. Line voltage version includes lamps and is provided with 6/25 watt self-ballasted 2700K spring lamps.

Certification

All fixtures are cULus listed for damp locations.

Options (consult factory)

26 watt CFQ 4-pin lamping

Custom finishes

24" stem/canopy kit (2) 6" & (1) 12" stems available, Model #DYKR24SN

Specifications and dimensions

subject to change without notice.

Ordering Information:

Satin Nickel	Qty.	Lamp	H	DIA.
DYP418SNMV	4	18W CFQ 4-Pin	9"	24"
DYP420SNSCTD	4	25W GU24 Dim	9"	24"
DYP618SNMV	6	18W CFQ 4-Pin	12"	30"
DYP620SNSCTD	6	25W GU24 Dim	12"	30"

