

S19-2100 (EFX25)

Emergency Fixture Thermostatic Mixing Valve

- Exceeds ANSI Z358.1
- Reliable Liquid-Filled Thermostat with 10-Year Warranty
- Integral Strainer Checkstops on Inlets
- Adjustable Set Point within Temperature Range
- Accurate Temperature Control to within ±3° F
- Built-in Cold Water Bypass, Assuring Cold Flow
- Positive Shutoff of Hot Supply When Cold Supply is Lost
- · Easy Installation and Serviceability
- Dirt and Lime Resistant
- Dial Thermometer
- · Factory Assembled and Tested
- Universal Mounting Capability
- · Cabinet Features:
 - 18 Gauge Body & Door
 - Left-Hand Hinge
 - Cylinder Lock
 - Inlet/Outlet Knock-Out Holes for Mounting Flexibility
 - Stainless Steel or Baked White Enamel Finishes
 - Surface-Mounted or Recessed Style

Valve Specifications

Maximum Operating Pressure

125 PSI (860 kPA)

Maximum Inlet Temperature

180° F (82° C)

Recommended Inlet Temperature

120° F (49° C) – 140° F (60° C)

Temperature Range Set Point Std. 65° F (18° C) to 95° F (35° C) 85° F (29° C)

Flow Capacities - GPM

Model	Min.	Pressure Drop – PSI							
Model	Flow	5	10	15	20	30	45	60	
\$19-2100	2.0	10.5	15.0	18.5	21.3	26.0	32.0	37.0	
Cold Bypa	ss Only	8.0	11.5	14.0	16.5	20.0	24.5	28.0	

Flow Capacities - L/Min

Model	Min.	Pressure Drop – Bar							
Model	Flow	.5	1.0	1.5	2.0	2.5	3.0	4.0	
\$19-2100	5.5	48.5	68.5	84.0	97.0	108.5	119.0	137.0	
Cold Bypas	ss Only	37.0	52.0	64.5	74.0	83.0	91.0	105.0	



This plumbing fixture is not intended to dispense water for human consumption through drinking or for preparation of food or beverages.



Va	lve	ΝЛ	~ 4	
Vа	IVE	IVI	uu	ıtı

Model Description

□ S19-2100 Emergency Fixture Thermostatic Mixing Valve

	Configurable	Valve	Model	(select one)		
Model	Description					
	□ EEV25		EEV25 T	hormostatic N		

EFX25 Thermostatic Mixing Valve with Options ☐ CAB-EFX25 EFX25 Thermostatic Mixing Valve Cabinet Only

Optional Valve Selections

Finish

 \square R Rough Brass (standard) \Box C Chrome Plated

Bracket

 \Box B Wall Mounting Bracket

□ **0** None

Piped Assembly

Piped Assembly with Inlet and Outlet Shutoff \square P

□ N* Piped Assembly only

 \Box 0 None

Optional Cabinet Selections

Cabinets (includes bracket)

Surface Mount Stainless Steel \square SS \square RS Recessed Stainless Steel □ SE Surface Mount White Enamel Recessed White Enamel \square RE

 \square 0 Window

 \square W Plexi-Glass Window in Door \square 0

*Requires cabinet selection



© 2019 Bradley

P.O. Box 309. Menomonee Falls. WI 53052-0309 800 BRADLEY (800 272 3539) +1 262 251 6000 bradleycorp.com


Page 1 of 4

Engineer's Approval_

6/26/2019 This information is subject to change without notice. Bradley_TMV_Emergency_EFX25





Recirculation Diagram (mm)




Dimensions

Model	Α	В	C	D	E	F	G	Н	X ^{NPT}	YNPT	Z ^{NPT}
S19-2100	7" (178)	2" (51)	3-1/8" (79)	5-1/4" (133)	9-5/8" (244)	14" (356)	2-3/4" (70)	9-3/16" (230)	3/4"	1"	3/4"









© 2019 Bradley
P.O. Box 309, Menomonee Falls, WI 53052-0309
800 BRADLEY (800 272 3539) +1 262 251 6000
bradleycorp.com

Dimensions — Surface-Mounted Cabinet


(mm)








Bottom View



Back View




Page 3 of 4 6/26/2019
This information is subject to change without notice.
Bradley_TMV_Emergency_EFX25


© 2019 Bradley
P.O. Box 309, Menomonee Falls, WI 53052-0309
800 BRADLEY (800 272 3539) +1 262 251 6000
bradleycorp.com



Dimensions — Recessed Cabinet

(mm)





Bottom View

