VITREOUS CHINA
TOILET

21-318



ULTRA FLUSH® Pressure-Assist Toilet 17" High, Elongated


12" Rough-in

Features:

- Low Consumption 1.6 gpf (6.0 Lpf)
- Elongated Bowl
- Extra Seat Height
- Pressurized Flushing Action
- Close Coupled Flushometer Tank
- Siphon Jet
- Front Tank Lever
- Optional Right-handed Trip Lever Available (Tank #28-380-97)
- Optional Locking Lid Available (Tank #28-380-LL)
- 2 Bolt Caps
- ADA Compliant


Dimensions:

Height30 1/2"		
Width20 1/4"		
Depth28 ³ / ₄ "		
Rough-in12"		
Water Surface from Rim4 1/2"		
Trapway (min)2"		
Water Surface12" x 10"		
Water Seal2 1/2"		
Shipping Weight 94 lbs		



Specifications: *Bowl*—#21-377 Elongated Bowl Seat not included

Tank-#28-380



THIS FIXTURE QUALIFIES
ACCORDING TO ASME TEST
PROCEDURES AS A LOW
CONSUMPTION WATER CLOSET
WITH AN AVERAGE CONSUMPTION
OF 1.6 GAL. OR LESS.






www.gerberonline.com

Job Name	
Date	
Model Specified	
Quantity	
Customer	
Contractor	
Architect/engineer	

(Bowl 21-377 with Tank 28-380)





NOTES:

All dimensions are in inches.

Illustrations may not be drawn to scale.

IMPORTANT:

Dimensions of fixtures are nominal and may vary within the range of tolerances established by ASME Standard A 112.19.2.

THIS FIXTURE QUALIFIES ACCORDING TO ASME TEST PROCEDURES AS A LOW CONSUMPTION WATER CLOSET WITH AN AVERAGE CONSUMPTION OF 1.6 gpf (6 Lpf) OR LESS.

VITREOUS CHINA