

Models:

3MFF100

Full Flow Drinking Water System

Spec #

Quantity

Applications:

- Chlorine Taste & Odor (CTO)
- Sediment
- Lead & Cryptosporidium parvum Cysts
- Select VOCs*

At a Glance:

- · Easy to install
- · Easy to replace cartridge
- 6,000 Gallon/22,712 liter Capacity
- 2.5 gpm/9.5 lpm Flow Rate
- 0.5 Nominal Micron Rating
- NSF listed (Std 42 and Std 53, CA and LA County Listed)
- CSA B483.1 Certified
- CA AB 1953 Certified



3MFF100

Product Benefits:


- 2.5 GPM allows filter system to be used on existing kitchen and /or bath faucets
- 3/8" NPT connections on filter head makes installation easy
- · Shut off valve in head eliminates the need to turn off water supply
- Sanitary quick change design helps eliminate the need to handle filter media
- Easy filter change-outs, just a 1/4 turn to remove and insert
- Designed to connect to your existing primary kitchen or bath faucet for full flow filtration, providing a clean look on your counter
- *This system reduces CTO, sediment, and a number of select VOCs (Benzene, p-Dichlorobenzene & Toxaphene), as well as lead and 99.95% of filterable *Cryptospo*ridium parvum cysts from your cold water supply delivered right to the sink

Physical Specifications:

Model No. (Part No.)	Inlet/ Outlet Size	Dimensions		Approximate			Мах.	Max.	Std.
		Height	Diameter	Weight	Flow Rate	Capacity	Water Temp.	Water Pressure	Replacement Ctg. No.
3MFF100 (56163-18)	3/8" NPT	16" (40.6 cm)	4-1/2" (11.4 cm)	4 lbs (1.8 kg)	2.5 gpm (9.5 lpm)	6,000 gallons (22,712 liters)	100 °F (37.8 °C)	125 psi (862 kPa)	56134-32
3MFF101 (56134-32)	N/A	14.5" (36.8 cm)		3.5 lbs (1.6kg)	N/A				N/A








Easy Installation:

CAUTION: Diagram shown is for reference purposes only. Read installation and operation manual prior to



Spec #

Quantity

Model Number

Part Number

Product Specifications:

- Includes head bracket with integral mounting bracket, 2 screws
- Inlet and outlet plumbing connections are 3/8" NPT design
- System max operating pressure of 125 psi (862 kPa) and max operating temperature of 100°F (37.8°C)
- Cartridge comprised of a pleated sub-micron membrane and composite activated carbon block filter
- 6,000 Gallon Capacity
- 2.5 gpm (9.5 lpm) flow rate
- 0.5 Nominal micron rating
- System is NSF Standard 42 & 53 compliant for the reduction of claims specified on the Performance Data Sheet
- Built in valve shuts off water when changing filters

How Big is a Micron? - A Micron is .000039 of an inch Relative Sizes

- Human eye can see 40 micron (a thousand times smaller than the eye of a needle)
- Diameter of a human hair is about 20 micron
- A Cryptosporidium parvum Cyst is 5-15 micron
- E.Coli Bacteria is 0.65 micron wide by 1.7 micron long
 The 3MFF100 does not reduce bacteria
- 3M Purification Inc. filter has pores 0.2 Micron in size

MARNING: To reduce the risk associated with the ingestion of contaminants: Do not use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before or after the system. Systems certified for cyst reduction may be used on disinfected water that may contain filterable cysts. EPA Establishment #070595-CT-001

CAUTION

To reduce the risk associated with property damage due to water leakage:

- Read and follow Use Instructions before installation and use of this system.
- The disposable filter cartridge MUST be replaced every 12 months, at the rated capacity or sooner if a noticeable reduction in flow rate occurs.

3M Purification Inc. recommends regularly scheduled maintenance and replacement of the filter cartridge(s) in order for the product to perform as advertised/sold.

Limited Warranty:

Limited Warranty: 3M Purification Inc. warrants the stainless steel head only to be free from defects in material and workmanship for one (1) year from the date of purchase. The disposable filter cartridge or membrane is warranted from defects in material and workmanship for a period of one (1) year from the date of purchase. This warranty does not cover failures resulting from abuse, misuse, alteration or damage not caused by 3M Purification Inc. or failure to follow installation and use instructions. No warranty is given as to the service life of any filter cartridge or membrane as it will vary with local water conditions and water consumption. 3M PURIFICATION INC. MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOMER OR DEALING, CUSTOMER OR

Limitation of Liability. 3M Purification Inc. will not be liable for any loss or damage arising from this 3M Purification Inc. product, whether direct, indirect, special, incidental, or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability. Some states and countries do not allow the exclusion or limitation of incidental or consequential damages, so the above limitation or exclusion may not apply to you.



3M Purification Inc.
400 Research Parkway
Meriden, CT 06450 U.S.A.
Toll Free: 1.800.222.7880
Worldwide: 203.237.5541
Fax: 203.238.8701
www.aquapure.com • www.3Mourification.com



System tested and Certified by NSF International against NSF/ANSI Standard 42 and 53 for the reduction of the claims specified on the Performance Data Sheet and against CSA B483.1.

Distributed by: