



MJ ACCESSORY PACK WITH GLAND

Product Features

Rubber Gasket


- Material - SBR
- Standard - ANSI / AWWA C111 / A21.11
- ASTM Test Methods
 - Hardness - D2240-91
 - Tensile Strength & Elongation - D412-92
 - Minimum Aging - D572-88
 - Maximum Compression - D395-89
 - NSF/ANSI Standard 61 Compliant

Ductile Iron Gland

- Material - ASTM A536, Grade 65-45-12
- Standard - ANSI / AWWA C153 / A21.53
- Coating - Asphaltic seal coat inside and out in accordance with ANSI / AWWA C104 / A24.1

Low Alloy Steel T-Head Bolts & Nuts


- Material & Dimension - ANSI / AWWA C111 / A21.11



Product Specifications

Includes Gland, MJ Gasket and Extra Long T-Head Bolts

PART #	SIZE
IMJAPK	2"
IMJAPM	3"
IMJAPP	4"
IMJAPU	6"
IMJAPX	8"
IMJAP10	10"
IMJAP12	12"
IMJAP14	14"
IMJAP16	16"



PROSELECT Glands, Gaskets, T-head Bolts and Mechanical Joint Accessory Packs are sold exclusively through Ferguson Enterprises and its affiliates.

Ferguson Enterprises guarantees the quality and compliance to the listed specifications.

PROSELECT is a registered trademark of Ferguson Enterprises.

Warranty and Codes

This PROSELECT product carries a 1-year limited warranty.