

Polyethylene Encasement Tubing

8 Mil Linear Low Density "Polywrap" for Ductile Iron Pipe

TRUMBULL POLYETHYLENE ENCASEMENT TUBING
protects metallic pipe in corrosive soils.

The tubing is slipped over the pipe, extended and taped. An overlap of approximately two feet should be figured in calculating the total polywrap required. For example, about 20 feet of polywrap is required for each 18 foot length, or 22 feet for each 20 foot length.

Made in the USA
Made per
ANSI/AWWA C105/A21.5-10



Black Polywrap

Pipe Size	Layflat Width	Weight lbs./ft.	Continuous		Perforated at 20 ft.		Perforated at 22 ft.		Tape Rolls Needed Per 1,000'
			Trumbull Item No.	Roll Length	Trumbull Item No.	Roll Length	Trumbull Item No.	Roll Length	
3"-6"	16"	0.106	388-9989	300 ft.	388-9942	300 ft.	388-9976	308 ft.	2
3"-8"	20"	0.132			388-9943	300 ft.	388-9961	308 ft.	3
10"	24"	0.159	388-9993	300 ft.	388-9945	300 ft.	388-9951	308 ft.	4
10"-12"	27"	0.179			388-9952	300 ft.	388-9962	308 ft.	4
14"-16"	34"	0.225	388-9996	300 ft.	388-9955	300 ft.	388-9966	308 ft.	6
16"-18"	37"	0.237	special order*		special order*		388-9967	308 ft.	7
18"-20"	41"	0.271	388-9998	300 ft.	388-9957	300 ft.	388-9969	308 ft.	7
24"	54"	0.358	388-9999	150 ft.	388-9958	160 ft.	388-9970	154 ft.	8
30"	67"	0.444	388-9985	150 ft.	special order*		388-9972	154 ft.	10
36"-42"	81"	0.536	388-9986	150 ft.	special order*		388-9974	154 ft.	15
48"	95"	0.629	388-9980	150 ft.	special order*		388-9975	154 ft.	17
54"-60"	108"	0.715	388-9982	150 ft.	special order*		388-9977	154 ft.	20
64"	121"	0.801	388-9984	150 ft.	special order*		special order*		21

* Indicates other sizes, types and colors that are available as "special order"; 4000# minimum per color, or size. See Price List for current sizes, colors & configurations stocked. 4 mil cross-laminated Polywrap also available.

Polywrap continues on the following page . . .