



PF92260 Thermoplastic Sump Pump

Product Features

- Tough thermoplastic construction
- SJE Rhombus vertical float switch
- 1-1/4" or 1-1/2" NPT Discharge
- Handles up to 1/8" solids
- Clog resistant impeller
- Carrying handle attached
- 10' power supply cord
- Built-in thermal overload protection for safety
- Permanent split capacitor continuous duty motor
- 3.8 amps, 456 Watts
- 3450 RPM




PF92260

Motor Performance

- 1/4HP 120 Volt AC (3.8 amps)

Performance Chart						
Lift	0'	5'	10'	15'	20'	25'
GPM	30	22	20	16	9	2
GPH	1800	1320	1200	960	540	120

Product Specifications



* All measurements are nominal. Please verify before actual installation.

Warranty and Codes

This product comes complete with installation, operating, care and maintenance instructions. This PROFLO sump pump carries a 3 year warranty when installed in residential applications. See owners manual for warranty details.

This PROFLO sump pump carries a 3 year limited warranty. In an effort to continually improve our products, we will make design changes from time to time. We reserve the right to ship newly designed product to fill any order unless it is agreed in writing to do otherwise.

