

PF73

Frost Proof Sillcocks



Product Features

- Provides hose connections outside of buildings
- Automatic draining when turned off and hose is removed so no water filled area is exposed to the outside freezing weather
- Wall hydrant with backflow preventer to avoid contamination of the building or public water system should there be a pressure drop (anti-siphon models only)
- PF73ASRK - Repair kit to include handle, anti-siphon and plunger assembly
- PF73ASHDL - Beige replacement handle
- Maximum operating pressure 125 PSI (water)
- Operating temperature range: 32° to 140°F

Model Numbers

PF73DP	1/2 X 4 bronze frost proof sillcock
PF73DU	1/2 X 6 bronze frost proof sillcock
PF73DX	1/2 X 8 bronze frost proof sillcock
PF73D10	1/2 X 10 bronze frost proof sillcock
PF73D12	1/2 X 12 bronze frost proof sillcock
PF73D14	1/2 X 14 bronze frost proof sillcock
PF73ASDCC	1/2cc bronze anti-siphon sillcock
PF73ASDP	1/2 X 4 bronze anti-siphon sillcock
PF73ASDU	1/2 X 6 bronze anti-siphon sillcock
PF73ASDX	1/2 X 8 bronze anti-siphon sillcock
PF73ASD10	1/2 X 10 bronze anti-siphon sillcock
PF73ASD12	1/2 X 12 bronze anti-siphon sillcock
PF73ASD14	1/2 X 14 bronze anti-siphon sillcock
PF73ASFP	3/4 X 1/2 X 4 brass anti-siphon sillcock
PF73ASFU	3/4 X 1/2 X 6 brass anti-siphon sillcock
PF73ASFX	3/4 X 1/2 X 8 brass anti-siphon sillcock
PF73ASF10	3/4 X 1/2 X 10 brass anti-siphon sillcock
PF73ASF12	3/4 X 1/2 X 12 brass anti-siphon sillcock
PF73ASF14	3/4 X 1/2 X 14 brass anti-siphon sillcock
PF73ASPXP	1/2 X 4 frost proof sillcock with PEX connection
PF73ASPXU	1/2 X 6 frost proof sillcock with PEX connection
PF73ASPXX	1/2 X 8 frost proof sillcock with PEX connection
PF73ASPX10	1/2 X 10 frost proof sillcock with PEX connection
PF73ASPX12	1/2 X 12 frost proof sillcock with PEX connection
PF73ASPX14	1/2 X 14 frost proof sillcock with PEX connection



PF73DP



PF73ASDCC



PF73ASPXP

Warranty and Codes

This PROFLO product carries a 1-year limited warranty. PF73D: CSA; PF73AS: CSA, UPC, ASSE-1019-A



PF73

Frost Proof Sillcocks



Product Specifications

No.	Description	Material	Special Notes
1	Body assembly	Brass	
2	Stem holder	Brass	
3	Packing	Rubber	
4	Name plate	Aluminum	
5	Nut	Brass	
6	Stem holder	Brass	
7	Spring	Stainless steel	
8	Plug axis	Brass	
9	O-ring	NBR	
10	Packing	Rubber	
11	Stem washer	Brass	
12	Seal	Rubber	
13	Screw	Brass	
14	Nut	Plastic	Anti-siphon models only
15	Screw	POM	Anti-siphon models only
16	Stem	POM	Anti-siphon models only
17	Seat	Brass	Anti-siphon models only
18	Handle	Zinc	
19	Set screw	Brass	



Model No.	A	B	C	D	Weight (lbs.)
PF73DP	1-1/4	4	3-5/8	2-3/4	1.03
PF73DU	1-1/4	6	3-5/8	2-3/4	1.07
PF73DX	1-1/4	8	3-5/8	2-3/4	1.11
PF73D10	1-1/4	10	3-5/8	2-3/4	1.15
PF73D12	1-1/4	12	3-5/8	2-3/4	1.19
PF73D14	1-1/4	14	3-5/8	2-3/4	1.23
PF73ASDCC	1-1/4	1-5/8	3-7/8	3-3/8	1.03
PF73ASDP	1-1/4	4	3-7/8	3-3/8	1.09
PF73ASDU	1-1/4	6	3-7/8	3-3/8	1.18
PF73ASDX	1-1/4	8	3-7/8	3-3/8	1.26
PF73ASD10	1-1/4	10	3-7/8	3-3/8	1.34
PF73ASD12	1-1/4	12	3-7/8	3-3/8	1.42
PF73ASD14	1-1/4	14	3-7/8	3-3/8	1.50
PF73ASFP	1-1/4	4	3-7/8	3-3/8	1.15
PF73ASFU	1-1/4	6	3-7/8	3-3/8	1.23
PF73ASFX	1-1/4	8	3-7/8	3-3/8	1.31
PF73ASF10	1-1/4	10	3-7/8	3-3/8	1.39
PF73ASF12	1-1/4	12	3-7/8	3-3/8	1.47
PF73ASF14	1-1/4	14	3-7/8	3-3/8	1.55
PF73ASPXP	1-1/4	4	3-7/8	3-3/8	1.09
PF73ASPXU	1-1/4	6	3-7/8	3-3/8	1.18
PF73ASPXX	1-1/4	8	3-7/8	3-3/8	1.26
PF73ASPX10	1-1/4	10	3-7/8	3-3/8	1.34
PF73ASPX12	1-1/4	12	3-7/8	3-3/8	1.42
PF73ASPX14	1-1/4	14	3-7/8	3-3/8	1.50

Warranty and Codes

This PROFLO product carries a 1-year limited warranty. PF73D: CSA; PF73AS: CSA, UPC, ASSE-1019-A