

PFCT100, PFCT101, PFCT103

Complete Toilet



General Specifications

- Vitreous china
- Includes two-piece toilet combination, toilet seat, flanges wx ring and flange bolts - all in one box
- Gravity fed (1.6 gpf/6.0 lpf)
- 2" fully glazed trapway
- Large 8-7/8" x 7-5/8" water surface area
- Close coupled tank with cover
- Color matched trip lever
- Available round front, elongated and ADA
- Anti-siphon fill valve

Model Numbers

- PFCT100WH** 2PC RF toilet with seat, wax rings and bolts, white
PFCT101WH 2PC EL toilet with seat, wax rings and bolts, white
PFCT103WH 2PC ADA toilet with seat, wax rings and bolts, white




PFCT101

	PFCT100	PFCT101	PFCT103
A	28-7/8"	28-7/8"	31-1/4"
B	15-3/4"	15-3/4"	15-3/4"
C	12"	12"	12"
D	8-3/8"	8-3/8"	8-3/8"
E	16-7/8"	18-3/4"	18-3/4"
F	14-5/8"	14-5/8"	17"

Warranty and Codes

This product comes complete with installation, operating, care and maintenance instructions. All PROFLO faucets carry a 1- year limited warranty. This product meets or exceeds ASME/ANSI A112.19.2M. In an effort to continually improve our products, we will make design changes form time to time. We reserve the right to ship newly designed product to fil any order unless we agree in writing to do otherwise.

Product Specifications



* All measurements are nominal. Please verify before actual installation

