



TWISTER TORNADO I



Sometimes you just need to cover your bases, so we designed these inexpensive power packs as simple, no-hassle solutions that blend in anywhere. Each hides powerful ventilation beneath the kitchen hood canopy of your choice, with three blower speeds and dual halogen lights. Decorative stainless steel filters add style. Just choose the ventilation level that's right for you and an optional, easy-to-install liner to complement your kitchen.



ESSENTIALS



Cabinet Bottom Cut-Out Size (W x D): AK8000AS and AK8100AS: 26 7/8" x 10 5/8".

POWER PACK TWISTER, TORNADO I

	MODEL	TWISTER - AK8000AS	TORNADO I - AK8100AS
POWER PACK	SIZE	27"	27"
	NET WIDTH	27 9/16"	27 9/16"
	PERFORMANCE		
	Internal Blower	180 - 290 CFM	200 - 600 CFM
	Internal Blower Sones	1.3 - 3.2	1.4 - 6
	COLOR		
	Stainless Steel	SS	SS
	FEATURES		
	Controls	Mechanical Slide	Mechanical Slide
	Speed Levels	3	3
	Auto Delay-Off	No	No
	Lighting	Halogen, 35W x 2	Halogen, 35W x 2
	Dual-Level Lighting	Yes	Yes
	Filters	Aluminum Mesh x 1	Decorative Mesh x 1
	Recirculating	Yes	No
	DUCT SPECIFICATIONS		
	Vertical	6"	6"
	Horizontal	NA	NA
	AC INPUT	120V - 60Hz	120V - 60Hz
	AC POWER	Max. 150W, 1.3 Amps	Max. 390W, 3.3 Amps
	OPTIONAL ACCESSORIES		
	30" Liner (17 1/8" - 20 1/2" Depth)	AK0800AS	AK0800AS
	36" Liner (17 1/8" - 20 1/2" Depth)	AK0836AS	AK0836AS
	Recirculating Kit	ZRC-0100	NA
Mounting Heights		Min. height 26" from cooking surface. Hood mounted 62" from floor.	Max. height 36" from cooking surface. Hood mounted 72" from floor.

