



aqualtherm green pipe® BALL VALVE without drain



Part no.	Dimension (ND — OD)	d	l	z	D	h	l1	Weight
		[in]	[in]	[in]	[in]	[in]	[in]	[lb]
0041308	½" — 20 mm	0.79	2.17	1.59	1.26	2.60	3.35	0.62
0041310	¾" — 25 mm	0.98	2.17	1.54	1.61	2.87	3.35	0.83
0041312	1" — 32 mm	1.26	2.50	1.79	1.85	3.23	4.25	1.31
0041314	1 ¼" — 40 mm	1.57	2.85	2.05	2.28	3.66	4.25	2.28
0041316	1 ½" — 50 mm	1.97	3.29	2.36	2.78	4.49	5.51	2.95
0041318	2" — 63 mm	2.48	4.04	2.95	3.43	5.20	5.51	5.63

aqualtherm green pipe® BALL VALVE HANDLE EXTENSION




Part no.	Dimension (ND — OD) x length	l	Weight
		[in]	[lb]
0041378	½" to ¾" — 20 to 25 mm x 35 mm	1.38	0.27
0041382	1" to 1 ¼" — 32 to 40 mm x 35 mm	1.38	0.27
0041386	1 ½" to 2" — 50 - 63 mm x 46 mm	1.81	0.60

Part no. 0041378 suitable for part no. 0041308 / 0041310.

Part no. 0041382 suitable for part no. 0041312 / 0041314.

Part no. 0041386 suitable for part no. 0041316 / 0041318.

aqualtherm green pipe® POLYPROPYLENE BALL VALVE



Part no.	Dimension (ND — OD)	d	l	z	D	h	L2	Weight
		[in]	[in]	[in]	[in]	[in]	[in]	[lb]
0041488	½" — 20 mm	0.79	2.03	1.46	1.81	2.01	2.68	0.26
0041490	¾" — 25 mm	0.98	2.30	1.67	2.20	2.40	3.07	0.41
0041492	1" — 32 mm	1.26	2.48	1.77	2.60	2.76	3.46	0.61
0041494	1 ¼" — 40 mm	1.57	2.83	2.03	3.11	3.19	3.86	0.96
0041496	1 ½" — 50 mm	1.97	2.99	2.07	3.43	3.54	4.25	1.21
0041498	2" — 63 mm	2.48	3.56	2.48	4.21	4.33	4.65	2.03
0041400	2 ½" — 75 mm	2.95	9.84	5.71	7.32	7.32	15.35	5.77