



aquatherm green pipe® REDUCING COUPLING

Socket welded on one side, butt welded on the other. These fittings can be used with either the **aquatherm green pipe®** or **aquatherm blue pipe®** systems, but are all molded from the green **fusiolen®** material. The SDR of the fittings must match the SDR of the pipe.



SDR	Part no.	Dimension (ND — OD)	d	d1	l	z	D	Weight
			[in]	[in]	[in]	[in]	[in]	[lb]
7.4	0111174	6" to 3 1/2" — 160 to 110 mm	6.30	4.33	3.43	1.97	5.79	1.59
	0111176	6" to 4" — 160 to 125 mm	6.30	4.92	3.54	1.97	6.57	1.80
	0111182	8" to 4" — 200 to 125 mm	7.87	4.92	5.31	3.74	6.57	3.53
11	0111175	6" to 3 1/2" — 160 to 110 mm	6.30	4.33	3.54	2.09	5.79	1.31
	0111177	6" to 4" — 160 to 125 mm	6.30	4.92	3.54	1.97	6.57	1.55
	0111183	8" to 4" — 200 to 125 mm	7.87	4.92	5.31	3.74	6.57	2.99
17.6	2511174	6" to 3 1/2" — 160 to 110 mm	6.30	4.33	3.54	2.09	5.79	-
	2511176	6" to 4" — 160 to 125 mm	6.30	4.92	3.54	1.97	6.57	1.39
	2511182	8" to 4" — 200 to 125 mm	7.87	4.92	5.31	3.74	6.57	2.33

aquatherm green pipe® ELBOW 90° (socket)



Part no.	Dimension (ND — OD)	d	z	l	D	Weight
		[in]	[in]	[in]	[in]	[lb]
0112108	1/2" — 20 mm	0.79	0.43	1.00	1.16	0.04
0112110	3/4" — 25 mm	0.98	0.53	1.16	1.34	0.05
0112112	1" — 32 mm	1.26	0.67	1.38	1.69	0.09
0112114	1 1/4" — 40 mm	1.57	0.83	1.63	2.05	0.16
0112116	1 1/2" — 50 mm	1.97	1.02	1.95	2.68	0.36
0112118	2" — 63 mm	2.48	1.28	2.36	3.31	0.64
0112120	2 1/2" — 75 mm	2.95	1.52	2.70	3.94	0.98
0112122	3" — 90 mm	3.54	1.81	3.11	4.72	1.64
0112124	3 1/2" — 110 mm	4.33	2.20	3.66	5.79	2.83
0112126	4" — 125 mm	4.92	3.01	4.59	6.57	4.42