



aqualtherm green pipe® NPT TRANSITION PIECE

With hex-shaped threaded transition



Industrial brass part no. (NPT)	Lead-free (potable) brass part no. (NPT)	Dimension PP-R (ND — OD) x thread	d	R	l	z	D	SW	Weight
			[in]	[in]	[in]	[in]	[in]	[in]	[lb]
0121308	0621308	(½" — 20 mm) x ½" M	0.79	0.50	2.62	2.05	1.52	0.87	0.23
0121310	0621310	(½" — 20 mm) x ¾" M	0.79	0.75	2.66	2.09	1.52	0.94	0.28
0121312	0621312	(¾" — 25 mm) x ¾" M	0.98	0.75	2.66	2.03	1.52	0.94	0.23
0121314	0621314	(1" — 32 mm) x 1" M	1.26	1.00	3.09	2.38	2.09	1.26	0.48
0121316	0621316	(1" — 32 mm) x 1 ¼" M	1.26	1.25	3.19	2.48	2.68	1.61	0.71
0121317	0621317	(1 ¼" — 40 mm) x 1" M	1.57	1.00	3.19	2.38	2.05	1.26	0.49
0121318	0621318	(1 ¼" — 40 mm) x 1 ¼" M	1.57	1.25	3.33	2.52	2.68	1.61	0.72
0121319	0621319	(1 ½" — 50 mm) x 1 ¼" M	1.97	1.25	3.37	2.44	2.68	1.61	0.78
0121320	0621320	(1 ½" — 50 mm) x 1 ½" M	1.97	1.50	3.48	2.56	2.91	1.81	0.95
0121321	0621321	(2" — 63 mm) x 1 ½" M	2.48	1.50	3.90	2.81	2.85	1.81	1.03
0121322	0621322	(2" — 63 mm) x 2" M	2.48	2.00	4.04	2.95	3.31	1.97	1.50
0121323	0621323	(2 ½" — 75 mm) x 2" M	2.95	2.00	4.09	2.91	3.31	1.97	1.61
0121324	0621324	(2 ½" — 75 mm) x 2 ½" M	2.95	2.50	4.13	2.95	3.94	2.56	2.14
0121325	0621325	(3" — 90 mm) x 3" M	3.54	3.00	4.96	3.66	4.72	3.35	2.90
0121327	-	(3 ½" — 110 mm) x 4" M	4.33	4.00	5.83	4.37	5.79	4.13	5.95

aqualtherm green pipe® TRANSITION ELBOW



Industrial brass part no. (NPT)	Stainless steel part no. (ISO)	Lead-free (potable) brass part no. (NPT)	Dimension PP-R (ND — OD) x thread	d	R	l	z	D	l1	z1	D1	Weight
				[in]	[in]	[in]	[in]	[in]	[in]	[in]	[in]	[lb]
0123008	0923008	0623008	(½" — 20 mm) x ¾" F	0.79	0.75	1.46	0.89	1.34	1.46	0.94	2.32	0.23
0123010	0923010	0623010	(½" — 20 mm) x ½" F	0.79	0.50	1.24	0.67	1.16	1.46	0.94	1.97	0.16
0123012	0923012	0623012	(¾" — 25 mm) x ¾" F	0.98	0.75	1.46	0.83	1.34	1.46	0.94	2.32	0.22
0123014	0923014	0623014	(¾" — 25 mm) x ½" F	0.98	0.50	1.34	0.71	1.34	1.46	0.94	2.07	0.16
0123016	0923016	0623016	(1" — 32 mm) x ¾" F	1.26	0.75	1.08	0.37	1.69	2.01	1.50	1.95	0.23
	(NPT)											
0123018	1123018	0623018	(1" — 32 mm) x 1" F	1.26	1.00	1.26	0.55	1.69	2.62	1.91	2.45	0.55