


Fig.1



Fig.2



- Made from cross-linked polyethylene PEX tubing
- Rated for a 400°F waterway
- Can be cut to length with PEX tubing cutter
- PROSELECT dip tubes & discharge tubes are certified to applicable parts of the following standards:
  - UL 174 "Household Electric Storage Tank Water Heaters"
  - UL 1453 "Booster and Commercial Storage Tank Water Heaters"
  - ANSI Z21.10 "Storage Water Heaters"
  - IAS 1-89 "Non-metallic Dip Tubes"
  - ANSI/NSF 61 "Drinking Water System Components Health Effects"
  - IAS/CSA 1-89, ANSI Z21.10.1 and Z21.10.3
  - ANSI Z21.98 "225°F temperature rating"
- UL & CSA certification files:
  - CSA Certificate of Compliance 1013314 (113104)
    [Master Contract 150236] for "Dip Tubes Nonmetallic"
  - UL MH25278 (cert to NSF 61)
  - UL MH17611 (cert to UL 174 and 1453)

DISCHARGE TUBE										
PROSELI	ECT PN	OLD Proselect Pn	DESCRIPTION	LENGTH	THREAD DIA.	PIC FOR FIGURE				
PSW125	507	PF9002273PK	3/4 T&P DCHRG PIPE	60"	3/4"	1				

DIP TUBES										
PROSEL	ECT PN	OLD Proselect Pn	DESCRIPTION	LENGTH	PIC FOR FIGURE					
PSW12	501	n/a	DIP TUBE UNIV	52"	2					

## **Warranty and Codes**

These PROSELECT products carry a 1-year limited warranty except where noted.