






CATALOG NUMBER	SCREW	DEAD FRONT	RECEPTACLE	RATING LABEL
U3822-20GR	1002771	1111312	1047264	1011753
U3822-20GWR	1002771	1111312	1047264	1137403
U3822-20R	1000062	1115163	1032578	1137403



ITEM NO.	QTY.	PART NUMBER	DESCRIPTION
1	1	1111320	SHELL WELDMENT
	1	1111325	BACK
	1	1111318	TOP
	1	1111308	BOTTOM
2	1	1002899	CONNECTOR, DUPLEX 4-14 AWG
3	2	1001290	SCREW, 10-32 X 5/16
4	1	1002472	60 AMP NON-FUSED PULLOUT
5	1	(SEE CHART)	SCREW, 10-32 x 3/8
6	1	(SEE CHART)	DEAD FRONT
7	1	(SEE CHART)	20 AMP GFI RECEPTACLE
8	2	1011618	SCW, 6-32 x .375 CRS PAN HD
9	1	1011757	LABEL- CAUTION
10	1	1111305	FRONT
11	1	SEE CHART	SEE CHART



LOCATE LABEL ON
BACK OF FRONT #11
ABOVE GFI
RECEPTACLE #9



CARTON: #1111791 6-PER

REV.	DATE	DESCRIPTION	BY
D1	7-13-05	CHARTED TOGETHER U3822-20GR REV. D & U3822-20R REV. C	TGS
D2	8-10-05	DELETED NOTE 1., ALT. 5880	TGS
E	3-9-09	ADDED INFORMATION FOR U3822-GWR IN CHART	EB

Material:			
Shear/ Die#:			
Finish:	MILBANK LIGHT GRAY	General Offices: Kansas City, MO	
Part Wt.:		Title: 60 AMP NON-FUSED DISCONNECT WITH 20 AMP RECEPTACLE	
Tolerances:		Catalog No.: (SEE CHART)	
Unless Specified Otherwise		Customer: MILBANK STD.	
X.X ±.1		Drawing No.: 3822	
X.XX ±.03		Date: 7-13-05	
X.XXX ±.015		Sheet 1 of 1	
X" ±2"			
Scale: NTS			
Drawn By: TGS			
Checked By:			
Approved By:			