



## Frigidaire 30" Freestanding Gas Range

Model: FFGF3053LS  
 29-7/8" W x 28-1/2" D x 47" H  
 MSRP: \$799.00

 Stainless Steel

### Specifications

Product Code: FFGF3053LS  
 Product Type: Ranges  
 Power Type: Gas  
 Size: 30"  
 Installation Type: Free-Standing  
 Color: Stainless Steel

#### Exterior Specifications

Manifold Panel: Color-Coordinated  
 Door Finish: Overlay  
 Handle Color: Stainless Steel

#### Cooktop Specifications

Cooking Surface: Upswept / Sealed Burners  
 Right Front: 14,000 BTU  
 Right Rear: 5,000 BTU  
 Left Front: 9,500 BTU  
 Left Rear: 9,500 BTU  
 Knob Type: Plastic  
 Grates: Individual  
 Grate Material: Cast Iron  
 Grate Color: Black Cast Matte

#### Oven Specifications

Oven 1 Type: Main  
 Oven 1 Bake: 18,000 BTU  
 Oven 1 Broil : 18,000 BTU  
 Oven 1 Broiling System: Vari-Broil™ High/Low  
 Oven 1 Rack Configuration: 2 Standard  
 Oven 1 Cleaning System: Self-Clean  
 Oven Window: XL Window

#### Exterior Dimensions

Height: 47"  
 Width: 29-7/8"  
 Depth: 28-1/2"  
 Depth (to Center of Arc): 28-1/2"  
 Depth (with Door 90° Open): 46-5/8"

### Electrical Specifications

Power Supply Connection Location: Rear Centerline  
Lower  
Voltage Rating: 120V, 60Hz

### General Specifications

Product Weight (lbs): 135  
Shipping Weight (lbs): 150

---