3000T3 Series — Electronic Faucet With Surface Mount Control Box and Single Inlet Supply	TECK [®] commercial		
Specification: (example)		3000T3 SERIES	/
 Supplied as complete product only H2OPrics® technology – no external adjustments required Chrome plated one piece cast main body with integral sensor Battery (4 'C' cell) or Hardwire (24 VAC) infrared electronic handwash system Field adjustable water resistant program controller with LCD screen Forged brass solenoid valve 			1 A

- Surface mount housing
- Mixing valve required (order separately)
- . Serviceable filter screen upstream of the valve
- and... with... (specify battery or hardwire)
 - with... (add spout variation required)
 - with... (add outlet required)

 - with... (Keyed Switch add suffix **-KS** if required See Next Page) with... (transformer for hardwire operation specify separately See Next Page)
- **Engineer/Architect Approval** Model Specified:

Approval:

Date:

	PRODUCT N	10.				
3000T3		0	Α		, E	
3001T3		0	Α			0
3000T3		0	Α	-BB]	
-	3001T3	3000T3 3001T3	3001T3 0	3000T3 0 A 3001T3 0 A	3000T3 0 A 3001T3 0 A	3000T3 0 A 3001T3 0 A



*Mixing valve (order separately). (1) Optional spouts R3, R7 and R35 only available in this series due to fixed gooseneck supplied. Refer to www.specselect.com for individual models.

Flow Rates are at 60 PSI. Note: Use these pages as product submittal sheets.

Delta reserves the right (1) to make changes in specifications and materials, and (2) to change or discontinue models, both without notice or obligation. Dimensions are for reference only. See current full-line price book or www.specselect.com for finish options and product availability.

DSP-3000TCB0 Rev. A



Approvals:

- CSA certified
- Complies to ASME A112.18.1/CSA B125.1
- Indicates compliance to ICC/ANSI A117.1
- 🕥 Outlet options 2, 3 and 7 are EPA WaterSense listed
- Verified compliant with 0.25% weighted average Pb content regulations

(Contact Delta Representative for State and/or Local Approvals.)

Patented



FINISHED WALL

24T3003

detailed specification.

OPERATION:

- Water flows when sensor is activated.
- Water flow stops at the selected run-on time after user removes hands from sensing zone. Run-on time selections are 0 to 8 seconds or 1 to 8 minutes for scrub-up applications. Factory set to 0 seconds.
- Blocking time between uses has selectable range of 1 to 8 seconds. Factory set to 1 second.
- Adjustable response time.
- Auto shut-off feature.
- Optional metered program mode with selection of 7 to 240 seconds of continuous operation.
- Adjustable sensing distance 76 to 381mm (3" to 15") factory set to 254mm (10") (± 3.0").





Switch. See DSP-ELACC for detailed specification

SPOUTS WITH SMOOTH ENDS



3000T & 3001T ELECTRONIC FAUCET OPTIONAL ACCESSORIES:

v	TRANSFORMERS:					
	060704A	110 to 24VAC Class II 20VA	(Up to 5 Electronic Valves)			
	060771A	110 to 24VAC Class II 40VA	(Up to 10 Electronic Valves)			
	060772A	110 to 24VAC Class II 100VA	(Up to 25 Electronic Valves)			
v	CORDS:					
	061256A	36" Cable Extension				

Note: Measurements may vary ± 6mm (0.25")

Refer to www.specselect.com for individual models.

Product supplied as shown by solid lines. All items shown by dotted lines supplied by others.

DSP-3000TCB0 Rev. A

Delta reserves the right (1) to make changes in specifications and materials, and (2) to change or discontinue models, both without notice or obligation. Dimensions are for reference only. See current full-line price book or www.specselect.com for finish options and product availability.

Specification Drawing #5





SURFACE MOUNT CONTROL BOX #0

3000T3	CEDIEC
300013	JEKIEJ

v	PRODUCT NO.		VALVE TYPE	COVER		
	3000T3		0	А	Wallmount Handwash Hardwire	Surface Mounted, Vandal Proof Control Housing
	3001T3		0	А	Wallmount Handwash Battery	Surface Mounted, Vandal Proof Control Housing



Note: Measurements may vary ± 6mm (0.25") Refer to www.specselect.com for individual models.

Delta reserves the right (1) to make changes in specifications and materials, and (2) to change or discontinue models, both without notice or obligation. Dimensions are for reference only. See current full-line price book or www.specselect.com for finish options and product availability.