

**PFXC1414M**



## Two Handle Gooseneck Kitchen Faucets

### Product Features

- 3 hole installation
- Flow rate: 1.75 GPM
- Metal lever handles
- Washerless design
- Max deck thickness: 1-1/8"
- 1/2" IPS connections
- Metal construction
- Meets ANSI:A112.18.1M
- NSF 61 compliant
- cUPC/IAPMO listed



**PFXC1414MCPLS**


### Model Numbers

<b>PFXC1414MCP</b>	Chrome with spray
<b>PFXC1414MCPLS</b>	Chrome less spray
<b>PFXC1414MBN</b>	PVD brushed nickel with spray
<b>PFXC1414MBNLS</b>	PVD brushed nickel less spray
<b>PFXC1414MORB</b>	Oil rubbed bronze with spray
<b>PFXC1414MORBLS</b>	Oil rubbed bronze less spray

### Available Parts

<b>PF141551PK</b>	Diverter
<b>PF141567PK</b>	Chrome decorative lever handle insert (pair)
<b>PF140330PK</b>	Chrome spray head, hose and guide
<b>PF143150PK</b>	Chrome 2.0 GPM decorative aerator
<b>PFX4LAVEXT</b>	Thick deck mounting kit

### Product Specifications



### Warranty and Codes

This product comes complete with installation, operating, care and maintenance instructions. This PROFLO faucet carries a 5-year limited warranty. This product meets ANSI: A112.18.1M. Compliant with lead content requirements of US Senate Bill S.3874.

