



**Precision Plumbing Products**

*"Specify with Confidence - Install with Pride"*

**PRIME-TIME ELECTRONIC TRAP PRIMING ASSEMBLY  
FLUSH MOUNT**

www.pppinc.net

It's PRIME-TIME to meet your floor drain trap priming needs. This unique trap priming assembly is available in 4 through 30 opening configurations and all the contractor needs to do is simply supply the potable water and power, Precision supplies the rest...

**"... Automatically maintains a constant water seal in floor drain traps."**

- Features:** ATMOSPHERIC VACUUM BREAKER  
 PRE-SET 24 HOUR CHANGE  
 MANUAL OVER RIDE SWITCH  
 120v/220v SOLENOID VALVE  
 120v/220v 3/WIRE CONNECTION  
 3/4" FNPT CONNECTION  
 CALIBRATED MANIFOLD FOR EQUAL  
 WATER DISTRIBUTION  
 5/8" OR 1/2" OUTLET COMPRESSION FITTINGS

**PT-4 4 OPENING MANIFOLD  
- THRU -**

**PT-2130 30 OPENING MANIFOLD**

**PART NUMBERS:**

**PT-4, PT-6, PT-8, PT-10, PT-12 PT-1320, PT-2130.**

The PRIME-TIME PRIMING ASSEMBLY will supply a minimum of 2 oz. of potable water at 20 P.S.I.G. at a preset factory setting of 10 seconds every 24 hours. The entire unit is pre-assembled in a steel cabinet ready to be flush wall mounted. The priming assembly must be mounted above the finished floor.

**MODEL # PT- \_\_\_\_\_**  
**PT-1320 - # of drains served: \_\_\_\_\_**  
**PT-2130 - # of drains served: \_\_\_\_\_**

(Please refer to list below for dimensions of cabinet models)

**CABINET DIMENSIONS:**

**MODEL # PT-4 - PT-12 ID Width 14" x Height 16"**  
**MODEL # PT-1320 ID Width 20 1/2" x Height 16 1/2"**  
**MODEL # PT-2130 ID Width 30 1/2" x Height 20 1/2"**

**PROJECT SUBMITTAL**

Project: \_\_\_\_\_

Contractor: \_\_\_\_\_

Engineer: \_\_\_\_\_

Date Submitted: \_\_\_\_\_

Prepared By: \_\_\_\_\_



**FLUSH MOUNT CABINET**

<b>COMPRESSION FITTINGS:</b>	
	1/2" COMP. FOR 3/8" ID COPPER LINE
	5/8" COMP. FOR 1/2" ID COPPER LINE <small>(This line is the floor drain trap make-up water line.)</small>
<b>CABINET: (16 GAUGE STEEL)</b>	
	DRY WALL, FLUSH MOUNT(IN WALL) <small>(CABINET DEPTH 4") (MOUNTING ANCHORS PROVIDED)</small>
	FIRE RATED, FLUSH MOUNT(IN WALL) <small>(CABINET DEPTH 6") (MOUNTING ANCHORS PROVIDED)</small>
<b>ACCESS DOOR: (DRY WALL)</b>	
	PRIME COAT
	STAINLESS STEEL
<b>ACCESS DOOR LATCH:</b>	
	SCREW DRIVER (Standard)
	ALLEN KEY
	CYLINDER LOCK
<b>ACCESS DOOR: (FIRE RATED)</b>	
	PRIME COAT
	STAINLESS STEEL
<b>ACCESS DOOR LATCH:</b>	
	RING PULL(Standard)
	CYLINDER LOCK
<b>VOLTAGE:</b>	
	120 Volt 60 Hz.
	240 Volts 60 Hz.

## SPECIFICATIONS

The Electronic Priming Assembly pictured is available in five separate configurations. The model PT-4 offers a four opening manifold capable of priming four separate floor drain traps from a single control unit. Models PT-6 thru PT-12 provide the same features only expanding to a total of twelve floor drains. All manifolds are available in either 1/2" or 5/8" compression fittings.



**Part Number: PT-4, PT-6, PT-8, PT-10, PT-12**

**Cabinet Dimension:  
ID 14"W x 16"H x 3-3/8"D**

**Access Door Part Number:  
D-1416PC  
D-1416SS**

The Electronic Priming Assembly pictured is available in a single configuration but is capable of priming from thirteen to twenty separate floor drain traps from a single control unit. The manifold is available in either 1/2" or 5/8" compression fittings. This model serves 13 to 20 drains.



**Part Number: PT-1320**

**Cabinet Dimension:  
ID 20-1/2" W x 16-1/2" H x 3-3/8" D**

**Access Door Part Number:  
D-1620PC  
D-1620SS**


The Electronic Priming Assembly pictured is available in a single configuration but is capable of priming from twenty one to thirty separate floordrain traps from a single control unit. The manifold is available in either 1/2" or 5/8" compression fittings. This model serves 21 to 30 drains.



**Part Number: PT-2130**

**Cabinet Dimension:  
ID 30-1/2"W x 20-1/2"H x 3-3/8"D.**

**Access Door Part Number:  
D-2030PC  
D-2030SS**



### DEPTH OF CABINET:

Standard 3-3/8", Fire Rated 6"

### INLET:

3/4" inch NPT female. ANSI/ASME BI.20.1.

### OUTLET:

5/8" or 1/2" inch compression fitting. SAEJ512.

### MANIFOLD:

3/4" Type "L" copper tubing. ASTM B88.

### SOLDERED JOINTS:

95-5 lead free containing lead not in excess of 0.2%.

### ELECTRICAL COMPONENTS:

Circuit Breaker, Test Switch, Timer, Solenoid Valve marked as UL listed.

Electronic assembly tested and certified per UL #73.

### BACKFLOW PREVENTION:

Anti-Siphon atmospheric vacuum breaker meets Los Angeles code, IAPMO, New York Board of Standards, ASSE 1001 and CSA.

### METAL CABINET:

16 gauge steel, galvanized.

### ACCESS DOOR:

Optional: Prime Coat, Stainless Steel, and Fire Rated.

NOTE: UNIT MUST BE INSTALLED PLUMB. - MUST BE INSTALLED WITH ACCESS. - All PRIME-TIME Flush Mount Units are available in Fire Rated Cabinets - 6" in Depth.

## Precision Plumbing Products

Division of JL Industries, Inc.

Airport Business Center  
 6807 NE 79th Court, Suite E  
 Portland, Oregon 97218

T (503) 256-4010  
 F (503) 253-8165

www.pppinc.net



JL Industries, Inc.



PATENT NO. 5,253,670

Rev 03/13