

PFP80VSSF Series

Van Stone Flange PVC Schedule 80




Features

- ANSI 150 lbs @ 73.4°F (23°C)
- Intended for applications where operating temperatures will not exceed 140°F (50°C)
- Socket diameters conform to ASTM D2467
- Bolt Hole Pattern conforms to ANSI B16.5; ASTM D4024
- Testing with compressed air or gas is not recommended
- Diameter conforms to ASME/ ANSI B16.5 class 150 Standard



Model Numbers

PFP80VSSFK	2 PVC SCH80 van stone SOC flange
PFP80VSSFL	2-1/2 PVC SCH80 van stone SOC flange
PFP80VSSFM	3 PVC SCH80 van stone SOC flange
PFP80VSSFP	4 PVC SCH80 van stone SOC flange
PFP80VSSFU	6 PVC SCH80 van stone SOC flange
PFP80VSSFX	8 PVC SCH80 van stone SOC flange



PFP80VSSFK

Model NO.	Size	A	B	C	D	E	F	G	H	I	J	Use Torque kfg - cm	Use Torque lbf - Feet
PFP80VSSFK	2" (50.8mm)	2.99	2.39	1.69	0.79	2.37	2.01	4.76	5.98	1.50	4.75	300	21.7
PFP80VSSFL	2-1/2" (63.5mm)	3.62	2.89	1.93	0.94	2.87	2.68	5.51	7.01	1.75	4.75	300	21.7
PFP80VSSFM	3" (76.2mm)	4.25	3.52	2.13	1.02	3.49	3.03	5.98	7.56	1.87	4.75	300	21.7
PFP80VSSFP	4" (101.6mm)	5.24	4.52	2.52	1.10	4.49	4.02	7.52	9.02	2.25	8.75	450	32.5
PFP80VSSFU	6" (152.4mm)	7.52	6.65	3.35	1.26	6.61	6.14	9.49	11.18	3.00	8.875	450	32.5
PFP80VSSFX	8" (203.2mm)	9.37	8.66	4.65	1.42	8.61	8.03	11.73	13.5	4.02	8.875	650	47

* All measurement are nominal. Please verify before actual installation

Warranty and Codes

This PROFLO product carries a 1-year limited warranty.