

REPAIR PARTS


GME95 Upflow 95% Furnace

GME950403BXAA

GME950603BXAA

GME950805CXAA

GME951005DXAA



This manual is to be used by qualified technicians only.

© 2009 Goodman Manufacturing Company, L.P. ♦ 5151 San Felipe, Suite 500 ♦ Houston, TX 77056

Important Information

Index

Functional Parts List	3
Illustration and Parts	4 - 13

Views shown are for parts illustrations only, not servicing procedures.

Text Codes:

AR - As Required

NA - Not Available

NS - Not Shown

00000000 - See Note

QTY - Quantity Example (QTY 3) (If Quantity not shown, Quantity = 1)

M - Model Example (M1) (If M Code not shown, then part is used on all Models)

Expanded Model Nomenclature:

Example

M1 - Model#1

M2 - Model#2

M3 - Model#3

Goodman Manufacturing Company, L.P. is not responsible for personal injury or property damage resulting from improper service. Review all service information before beginning repairs.

Warranty service must be performed by an authorized technician, using authorized factory parts. If service is required after the warranty expires, Goodman Manufacturing Company, L.P. also recommends contacting an authorized technician and using authorized factory parts.

Goodman Manufacturing Company, L.P. reserves the right to discontinue, or change at any time, specifications or designs without notice or without incurring obligations.

For assistance within the U.S.A. contact:

Consumer Affairs Department

Goodman Manufacturing Company, L.P.

7401 Security Way

Houston, Texas 77040

877-254-4729-Telephone

713-863-2382-Facsimile

For assistance outside the U.S.A. contact:

International Division

Goodman Manufacturing Company, L.P.

7401 Security Way

Houston, Texas 77040

713-861-2500-Telephone

713-863-2382-Facsimile

Functional Parts

Part

No: Description:

0130F00010	FLAME SENSOR
B1370818	INTERLOCK SWITCH
10123519	MANUAL RESET LIMIT (M4)
10123517	MANUAL RESET LIMIT (M3)
10123535	MANUAL RESET LIMIT-RED (M1, M2, M3)
10123533	MANUAL RESET LIMIT-YELLOW (M1, M2, M4)
0131M00286	MOTOR, 115V 1 HP, PROG (M3)
0131M00287	MOTOR, 115V 1 HP, PROG (M4)
0131M00285	MOTOR, 115V 1/2 HP, PROG (M2)
0131M00284	MOTOR, 115V 1/2 HP, PROG (M1)
0130F00214	PRESSURE SWITCH (M1)
0130F00110	PRESSURE SWITCH - GREEN (M2, M3, M4)
20197308	PRESSURE SWITCH-YELLOW
0130M00063	PRIMARY LIMIT - GOLD 140° (M2, M3)
20162904	PRIMARY LIMIT-TEMPERATURE CONTROL (M1, M4)
0130F00008S	SINI IGNITOR
B1141605	TRANSFORMER 120V TO 24V, 40 VA
0151M00014S	VALVE, GAS (HW) VR92

SPECIAL PARTS



0161F00000P GOODMAN NAMEPLATE

Expanded Model Nomenclature

M1 - GME950403BXAA
M2 - GME950603BXAA
M3 - GME950805CXAA
M4 - GME951005DXAA

Cabinet

Image 1



Cabinet

**Ref. Part
No: No:**

Description:

**Ref. Part
No: No:**

Description:

Image 1:

21	0161F00000P	GOODMAN NAMEPLATE
111	20179308	GASKET (QTY 2)
121	20179311	GASKET
131	20179312	GASKET (M3)
131	20179313	GASKET (M4)
191	0121F00072DGS	ACCESS DOOR (M1, M2)
191	0121F00073DGS	ACCESS DOOR (M3)
191	0121F00074DGS	ACCESS DOOR (M4)
201	0121F00069DGS	BLOWER DOOR (M1, M2)
201	0121F00070DGS	BLOWER DOOR (M3)
201	0121F00071DGS	BLOWER DOOR (M4)
281	B1392139	VIEW PORT BUSHING-BLOWER DOOR (QTY 2)
331	0161F00012S	JUNCTION BOX-PLA
451	M0501301	PIPE GROMMET
491	M0570808	BUTTON PLUG (QTY 4)
501	M0570806	BUTTON PLUG
511	M0570807	BUTTON PLUG
601	A4691701	GROMMET (QTY 2)
621	M0310345	BUTTON PLUG (QTY 2)

Image 2:

12	10254303	RUBBER COUPLING
22	0163M00049	HOSE CLAMP (QTY 2)
32	M0119207	HOSE CLAMP
62	20201901	DRAIN HOSE
72	20201902	DRAIN HOSE
82	20171701	DRAIN TRAP
112	20214203	DRAIN ANGLE
142	M0119205	HOSE CLAMP (QTY 3)
152	B2810816	2" MESH INSERT
162	B2810814	3" MESH INSERT
172	M0119206	HOSE CLAMP

Expanded Model Nomenclature

M1 - GME950403BXAA
M2 - GME950603BXAA
M3 - GME950805CXAA
M4 - GME951005DXAA

Blower Assembly

Image 1





Image 2



Blower Assembly

Ref. Part No: No:	Description:	Ref. Part No: No:	Description:
----------------------	--------------	----------------------	--------------

Image 1:

21	B1368047A	BLOWER WHEEL 10 X 10 (M3)
21	B1368058S	BLOWER WHEEL 10 X 8 (M1, M2)
51	764741F	BLOWER BLOCK-OFF 10 X 10 (M3)
51	764740F	BLOWER BLOCK-OFF 10 X 8 (M1, M2)
231	M0250558	TC SCREW (M1, M2, M3)
461	0121F00025P	CONTROL BRACKET
481	B1141605	TRANSFORMER 120V TO 24V, 40 VA
601	B1392021	PLASTIC PLUG, 1" (2713-BLK) (M1, M2, M3)
NS	0130M00073	ECOTECH POWER HARNESS
NS	B1393802	SUPPORT, 2-WING BOARD, .187 MT (QTY 4)
NS	B1393803	SUPPORT, SINGLE-WING BOARD (.1
NS	0159F00018	WIRING HARNESS

Image 2:

22	D6723311S	BLOWER WHEEL (M4)
42	A4002702	BLOWER MOTOR GROMMET (QTY 3)
142	10441601	MOTOR MOUNT BAND (M4)
152	10441501	MOTOR MOUNT ARM (M4)
182	0131M00286	MOTOR, 115V 1 HP, PROG (M3)
182	0131M00287	MOTOR, 115V 1 HP, PROG (M4)
182	0131M00284	MOTOR, 115V 1/2 HP, PROG (M1)
182	0131M00285	MOTOR, 115V 1/2 HP, PROG (M2)
192	0271F00003PS	BLOWER HOUSING ASSY 10 X 10 (M3)
192	0271F00000P	BLOWER HOUSING ASSY 10 X 8 (M1, M2)
192	0271F00048	BLOWER HOUSING ASSY 11 X 10 (M4)
232	M0221461	TC SCREW (QTY 3)

Image 6:

86	20175101	BLOWER SIDE RAIL (M4)
----	----------	-----------------------

Expanded Model Nomenclature

M1 - GME950403BXAA
M2 - GME950603BXAA
M3 - GME950805CXAA
M4 - GME951005DXAA

Chassis

Image 1





Image 2



Chassis

Ref. Part No: No:	Description:	Ref. Part No: No:	Description:
----------------------	--------------	----------------------	--------------

Image 1:

11	0121F00050DGS	BASE PAN (M1, M2)
11	0121F00051DGS	BASE PAN (M3)
11	0121F00052DG	BASE PAN (M4)
31	0121F00045	BLOWER DECK (M3)
31	0121F00048	BLOWER DECK (M4)
31	0121F00043S	DECK-BLWR UF 17.5 FUR (M1, M2)
41	0154F00000P	COIL GASKET (M1, M2)
41	0154F00001P	COIL GASKET (M3)
41	0154F00002P	COIL GASKET (M4)
41	20215701S	GASKET-FA
81	20273208	BACK PANEL (M1, M2)
81	20273212S	PANEL-BACK UF FURN (M4)
81	20273210S	PANEL-BACK UF PNT (M3)
101	0121F00018P	DECK RAIL (M1, M2)
101	0121F00019P	DECK RAIL (M3)
101	20191303	DECK RAIL (M4)
111	0270F00001PS	TOP COVER ASSY (M3)
111	0270F00002PS	TOP COVER ASSY (M4)
111	0270F00100PS	TOP COVER ASSY (M1, M2)
121	20191602	SIDE RAIL (M1, M2)
121	20191603	SIDE RAIL (M3)
121	20191604	SIDE RAIL (M4)
141	0121F00092DGS	SIDE PANEL LH
151	0121F00090DGS	SIDE PANEL RH
221	B1370818	INTERLOCK SWITCH
231	22309501	FLUE PIPE
241	20171802S	ELBOW
271	22307501S	ID BLOWER
281	20049701	FA COUPLING
311	22320001	DECK GASKET (M1, M2)
311	22320002	DECK GASKET (M3)
311	22320003	DECK GASKET (M4)
591	11165107	ID BLOWER SHIELD
741	B1392104	UNIVERSAL BUSHING UB 875
811	20194607	GASKET

Image 2:

352	10861101	AUXILIARY LIMIT BRACKET
522	10123519	MANUAL RESET LIMIT (M4)
522	10123535	MANUAL RESET LIMIT-RED (M1, M2, M3)

Expanded Model Nomenclature

M1 - GME950403BXAA
M2 - GME950603BXAA
M3 - GME950805CXAA
M4 - GME951005DXAA

This exploded perspective view illustrates the assembly of a multi-channel flow control device. The main components are shown in an exploded state to reveal their internal structure and assembly sequence. Key parts include:

- 31**: A central rectangular frame or base plate.
- 61**: A curved inlet pipe or channel on the left side.
- 71**: A series of parallel channels or slots on the top surface of the frame.
- 151**: A series of parallel channels or slots on the bottom surface of the frame.
- 91**: A rectangular plate or cover on the right side.
- 321**: A series of parallel channels or slots on the right side of the frame.
- 301**: A circular component, likely a valve or connector, at the bottom left.
- 291**: A circular component, likely a valve or connector, at the bottom center.
- 21**: A complex mechanical component, possibly a pump or actuator, at the bottom right.
- 11**: A vertical support or guide post.
- 41**: A vertical support or guide post.
- 371**: A circular component, likely a valve or connector, at the bottom right.

The assembly is shown in an exploded state, with dashed lines indicating the alignment and assembly path of the various components.

Manifold / Gas Valve

Ref. Part No: No:	Description:	Ref. Part No: No:	Description:
----------------------	--------------	----------------------	--------------


Image 1:

11	0164M00002	PRESSURE SWITCH HOSE (QTY 2)
11	0130F00008S	SINI IGNITOR
21	0151M00014S	VALVE, GAS (HW) VR92
31	0163F00004	ORIFICE
41	0130F00010	FLAME SENSOR
61	20196401	MANIFOLD - 2 BRNR (M3)
61	20196402	MANIFOLD - 3 BRNR (M1)
61	20196403	MANIFOLD - 4 BRNR (M2)
61	20196404	MANIFOLD - 5 BRNR (M4)
71	10735102S	BECKETT BURNER (QTY 2)
91	20190410	BURNER BRACKET 2B (M1)
91	20190411	BURNER BRACKET 3B (M2)
91	20190412	BURNER BRACKET 4B (M3)
91	20190413	BURNER BRACKET 5B (M4)
151	10123517	MANUAL RESET LIMIT (M3)
151	10123533	MANUAL RESET LIMIT-YELLOW (M1, M2, M4)
291	0130F00214	PRESSURE SWITCH (M1)
291	0130F00110	PRESSURE SWITCH - GREEN (M2, M3, M4)
301	20197308	PRESSURE SWITCH-YELLOW
321	11072201	ORIFICE SHIELD (M1)
321	11072202	ORIFICE SHIELD (M2)
321	11072203	ORIFICE SHIELD (M3)
321	11072204	ORIFICE SHIELD (M4)
371	0130M00063	PRIMARY LIMIT - GOLD 140° (M2, M3)
371	20162904	PRIMARY LIMIT-TEMPERATURE CONTROL (M1, M4)
NS	0164M00002	PRESSURE SWITCH HOSE
NS	0164M00009	PRESSURE SWITCH HOSE
NS	0164M00011	PRESSURE SWITCH HOSE (M1)
NS	0164M00012	PRESSURE SWITCH HOSE (M2)
NS	0164M00013	PRESSURE SWITCH HOSE (M3)
NS	0164M00014	PRESSURE SWITCH HOSE (M4)

Expanded Model Nomenclature

M1 - GME950403BXAA
M2 - GME950603BXAA
M3 - GME950805CXAA
M4 - GME951005DXAA

Heat Exchanger



Heat Exchanger

Ref. Part

No: No:

Description:

Ref. Part

No: No:

Description:

Image 1:

51	0270F01955	HEAT EXCHANGE ASSY (M2)
51	0270F01956	HEAT EXCHANGE ASSY (M3)
51	0270F01957	HEAT EXCHANGE ASSY (M1)
51	0270F01958	HEAT EXCHANGE ASSY (M4)
131	20170810A	COVER, FRONT (M1)
131	20170811A	COVER, FRONT (M2)
131	20170909A	COVER-FRONT (M3)
131	20171007A	COVER-FRONT (M4)
141	20215701S	GASKET-FA
231	A1781105	CAP-VINYL .500 (QTY 2)

Expanded Model Nomenclature

M1 - GME950403BXAA
M2 - GME950603BXAA
M3 - GME950805CXAA
M4 - GME951005DXAA