

Item #: <b>P5040-077-L</b>	UPC Code: 844349010661
Product Family Name: <b>Tube</b>	Finish: <b>Chrome</b>
Category: <b>Wall Sconce</b>	Category Type: <b>Sconce</b>
Certification <b>4006873</b>	
Patents	
Notes: The glass thickness increased from 2.0mm to at least 2.5mm per PRN 8/8/2014	



Image File Name:  
P5040-077-L--  
1377187721.jpg



## MEASUREMENTS

Width: <b>4.75</b>	Length: <b>13.25</b>	Height: <b>13.25</b>	Extension: <b>4</b>
Height Adjustable: <b>No</b>	Min Overall Height:	Max Overall Height:	Slope: <b>No</b>
Wire Length: <b>7</b>	Chain Length:	Safety Cable Included: <b>No</b>	Net Weight: <b>3.11</b>
Canopy Width: <b>4.75</b>	Canopy Height: <b>6.5</b>	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top: <b>9.25</b>	Center to Bottom: <b>3.25</b>

## LAMPING

No. of Bulbs: <b>1</b>	Light Type: <b>L-L10-Moduleled</b>			
Max Bulb Wattage: <b>10</b>	Socket: <b>Led</b>			
Dimmable: <b>Yes</b>	Ballast:	Rated Life Hours: <b>30000</b>	Photocell included:	Lamps included: <b>Yes</b>
LED Included: <b>Yes</b>	Color Temp.: <b>3000</b>	CRI: <b>98</b>	Initial Lumens: <b>867</b>	Delivered Lumens: <b>606</b>



## SHIPPING

Carton Width: <b>7.75</b>	Carton Height: <b>5.5</b>	Carton Length: <b>14.75</b>	
Carton Weight: <b>3.96</b>	Carton Cubit Feet: <b>0.364</b>	Small Package Shippable: <b>Yes</b>	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack: <b>1</b>

## SHADE / GLASS

Description:	Material: <b>Glass</b>	
Part No.: <b>PG5040</b>	Quantity: <b>1</b>	
Width: <b>2.38</b>	Height: <b>10.63</b>	Length:

**LED**



LED

Yes

ADA Compliant

Yes

Damp Location

Yes

Title 17

Yes

ETL Intertek

Yes