

Features

- Metal construction.
- Includes showerhead with arm and flange.
- Includes faceplate and lever handle.
- 2.0 gal/min (7.6 l/min) maximum flow rate.

Required Accessories

K- 2971-KS 3/4" Pressure-balancing Valve

or

K- 304-CS Pressure-balancing Valve With Stops

or

K- 304-CX Pressure-balancing Valve Less Stops

or

K- 304-K Pressure-balancing Valve Less Stops

or

K- 304-KS Pressure-balancing Valve With Stops

or

K- 304-PS Pressure-balancing Valve With Stops

or

K- 304-PX Pressure-balancing Valve Less Steps

or

K- 304-US Pressure-balancing Valve With Stops

or

K- 304-UX Pressure-balancing Valve Less Stops

Optional Accessories

88526 Thin Wall Trim Kit



Codes/Standards

ASME A112.18.1/CSA B125.1


ASSE 1016

DOE - Energy Policy Act 1992

EPA WaterSense®

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Showerhead:

Rated maximum flow: 2 gal/min (7.6 l/min)

Pressure: 80 psi (5.5 bar)

Notes

For use with automatic compensating valves rated at 1.7 gal/min (6.4 l/min) or less.

Install this product according to the installation guide.

NOTICE: Risk of product damage. Long screws, for installing trim, can damage the K-2971-KS valve. Consult the trim installation guide to verify if the thin wall installation kit (88526) is needed.

Avoid cross-flow conditions. Do not install shut-off device on either valve outlet.

Install straight pipe or tube drop of 7" (178 mm) to 18" (457 mm) with single elbow between valve and wall-mount spout.