

PF73

Frost Proof Sillcocks



Product Features

- Provides hose connections outside of buildings
- Automatic draining when turned off and hose is removed so no water filled area is exposed to the outside freezing weather
- Wall hydrant with backflow preventer to avoid contamination of the building or public water system should there be a pressure drop (anti-siphon models only)
- PF73ASRK1 - Repair kit to include handle, anti-siphon and plunger assembly
- PF73ASHDL - Beige replacement handle
- PF73RK - the handle, seal and washer repair kits for non anti-siphon PF73
- Maximum operating pressure 125 PSI (water)
- Operating temperature range: 32° to 140°F
- Not for potable use

Model Numbers

PF73DP	1/2 X 4 brass frost proof sillcock
PF73DU	1/2 X 6 brass frost proof sillcock
PF73DX	1/2 X 8 brass frost proof sillcock
PF73D10	1/2 X 10 brass frost proof sillcock
PF73D12	1/2 X 12 brass frost proof sillcock
PF73D14	1/2 X 14 brass frost proof sillcock
PF73ASDCC	1/2cc brass anti-siphon sillcock
PF73ASDP	1/2 X 4 brass anti-siphon sillcock
PF73ASDU	1/2 X 6 brass anti-siphon sillcock
PF73ASDX	1/2 X 8 brass anti-siphon sillcock
PF73ASD10	1/2 X 10 brass anti-siphon sillcock
PF73ASD12	1/2 X 12 brass anti-siphon sillcock
PF73ASD14	1/2 X 14 brass anti-siphon sillcock
PF73ASFP	3/4 X 1/2 X 4 brass anti-siphon sillcock
PF73ASFU	3/4 X 1/2 X 6 brass anti-siphon sillcock
PF73ASFX	3/4 X 1/2 X 8 brass anti-siphon sillcock
PF73ASF10	3/4 X 1/2 X 10 brass anti-siphon sillcock
PF73ASF12	3/4 X 1/2 X 12 brass anti-siphon sillcock
PF73ASFF12	3/4 X 3/4 X 12 brass anti-siphon sillcock
PF73ASPXP	1/2 X 4 brass anti-syphon sillcock with F1807 pex connection
PF73ASPXU	1/2 X 6 brass anti-syphon sillcock with F1807 pex connection
PF73ASPXX	1/2 X 8 brass anti-syphon sillcock with F1807 pex connection
PF73ASPX10	1/2 X 10 brass anti-syphon sillcock with F1807 pex connection
PF73ASPX12	1/2 X 12 brass anti-syphon sillcock with F1807 pex connection
PF73ASPPP	1/2X4 brass anti-syphon sillcock with F1960 pex connection
PF73ASPPU	1/2X6 brass anti-syphon sillcock with F1960 pex connection
PF73ASPPX	1/2X8 brass anti-syphon sillcock with F1960 pex connection
PF73ASPP10	1/2X10 brass anti-syphon sillcock with F1960 pex connection
PF73ASPP12	1/2X12 brass anti-syphon sillcock with F1960 pex connection



PF73DP



PF73ASDCC



PF73ASPXP



PF73ASPPP

Warranty and Codes

This PROFLO product carries a 1-year limited warranty. PF73D: CSA; PF73AS: CSA, UPC, ASSE-1019-A ; PF73ASPP: CSA, UPC



PF73

Frost Proof Sillcocks



Product Specifications

No.	Description	Material	Special Notes
1	Body assembly	Brass	
2	Stem holder	Brass	
3	Packing	Rubber	
4	Name plate	Aluminum	
5	Nut	Brass	
6	Stem holder	Brass	
7	Spring	Stainless steel	
8	Plug axis	Brass	
9	O-ring	NBR	
10	Packing	Rubber	
11	Stem washer	Brass	
12	Seal	Rubber	
13	Screw	Brass	
14	Nut	Plastic	Anti-siphon models only
15	Screw	POM	Anti-siphon models only
16	Stem	POM	Anti-siphon models only
17	Seat	Brass	Anti-siphon models only
18	Handle	Zinc	
19	Set screw	Brass	



Model No.	A	B	C	D	Stem Length
PF73DP	1-1/4	4	3-5/8	2-3/4	7
PF73DU	1-1/4	6	3-5/8	2-3/4	9
PF73DX	1-1/4	8	3-5/8	2-3/4	11
PF73D10	1-1/4	10	3-5/8	2-3/4	13
PF73D12	1-1/4	12	3-5/8	2-3/4	15
PF73D14	1-1/4	14	3-5/8	2-3/4	17
PF73ASDCC	1-1/4	1-5/8	3-7/8	3-3/8	5-1/2
PF73ASDP	1-1/4	4	3-7/8	3-3/8	7-15/16
PF73ASDU	1-1/4	6	3-7/8	3-3/8	9-15/16
PF73ASDX	1-1/4	8	3-7/8	3-3/8	11-15/16
PF73ASD10	1-1/4	10	3-7/8	3-3/8	13-15/16
PF73ASD12	1-1/4	12	3-7/8	3-3/8	15-15/16
PF73ASD14	1-1/4	14	3-7/8	3-3/8	17-15/16
PF73ASFP	1-1/4	4	3-7/8	3-3/8	7-15/16
PF73ASFU	1-1/4	6	3-7/8	3-3/8	9-15/16
PF73ASFX	1-1/4	8	3-7/8	3-3/8	11-15/16
PF73ASF10	1-1/4	10	3-7/8	3-3/8	13-15/16
PF73ASF12	1-1/4	12	3-7/8	3-3/8	15-15/16
PF73ASFF12	1-1/4	12	3-7/8	3-3/8	15-15/16
PF73ASPXP	1-1/4	4	3-7/8	3-3/8	7-15/16
PF73ASPXU	1-1/4	6	3-7/8	3-3/8	9-15/16
PF73ASPXX	1-1/4	8	3-7/8	3-3/8	11-15/16
PF73ASPX10	1-1/4	10	3-7/8	3-3/8	13-15/16
PF73ASPX12	1-1/4	12	3-7/8	3-3/8	15-15/16
PF73ASPPP	1-1/4	4	3-7/8	3-3/8	7-15/16
PF73ASPPU	1-1/4	6	3-7/8	3-3/8	9-15/16
PF73ASPPX	1-1/4	8	3-7/8	3-3/8	11-15/16
PF73ASPP10	1-1/4	10	3-7/8	3-3/8	13-15/16
PF73ASPP12	1-1/4	12	3-7/8	3-3/8	15-15/16

Warranty and Codes

This PROFLO product carries a 1-year limited warranty. PF73D: CSA;
PF73AS: CSA, UPC, ASSE-1019-A ; PF73ASPP: CSA, UPC