

APak® Alarm Systems

The all new APak® alarm is more compact and easier to install. It is CSA approved in a NEMA 1 enclosure. Battery life is over 1 year from 2 AA batteries. Alarm may be used as AC only, DC only, or AC/DC applications. The APak® alarm system sounds a horn when a potentially threatening liquid level condition occurs. The horn can be silenced, but the alarm light remains on until the condition is remedied.

A green "POWER ON" light indicates 120 V primary power to the alarm. A low battery chirp feature indicates when the battery should be replaced. A red "ALARM" light indicates a high-level condition.

NOTE: It is always recommended to power the alarm from a separate circuit than the pump to avoid losing power to both during a tripped breaker scenario.



10-4012

SPECIFICATIONS:

- NEMA 1 enclosure (INDOOR USE ONLY)
- Automatic alarm reset
- Horn is rated 87 decibels at 10' (3 m)
- 2 AA battery backup (battery not included)
- 15' (5 m) alarm (12 V) tethered switch
- 6' (2 m) power cord
- Auxiliary dry contacts (use 10-4014)



10-4011

SPECIFICATIONS:

- Same standard features of our 10-4012 with:
- 15' (5 m) alarm reed switch
 - Auxiliary dry contacts (use 10-4013)

Z Control® Enabled Models 10-4013 and 10-4014

SPECIFICATIONS:

- 10-4013 comes with reed sensor
- 10-4014 comes with mechanical float switch
- All the standard features plus:
- 2nd input for additional monitoring ability
- Dry contacts for connection to home security system, etc.
- Z Control Enabled
 - Wi-Fi® equipped
 - Receive free text, email, and push alerts on:
 - Power outage
 - Low battery
 - Input 1 or 2 triggers
 - Loss of contact with Z Control®
 - Remotely silence, reset alarm.
 - Free Z Control App and Web interfaces
 - Free Z Control account
 - No monthly cost
 - Simple setup
 - Z Control connectivity LED



10-0623 Indoor/Outdoor

SPECIFICATIONS:

- NEMA 3R enclosure (6.5" x 4.5" x 3") (16.5 x 11.4 x 7.6 cm)
- Top-mounted alarm beacon
- Automatic alarm reset, horn silence switch and alarm test switch
- Horn is rated 85 decibels at 10' (3 m)
- Pre-mounted terminal block with connections for pump and float switch
- 15' (5 m) alarm (12 V) tethered switch
- Power connections are field-wired



NOTE: All variable level float switches in this section are mechanically activated and do not contain mercury.

10-0682 Deluxe

SPECIFICATIONS:

- Same standard features of our 10-0623 with:
- 20' (6 m) alarm (12 V) tethered switch
 - 6' (2 m), 115 V power cord with water-tight cord connectors

10-0126 Indoor/Outdoor

SPECIFICATIONS:

- Same standard features of our 10-0623 with:
- NEMA 4X thermoplastic enclosure (6" x 4" x 3") (15.2 x 10.2 x 7.6 cm)
 - Horn is rated 88 decibels at 10' (3 m)
 - 5A auxiliary dry contacts

