

PARTS LIST

GALAXY

CAST-IRON GAS BOILERS

GG Series, Hot Water Models

ITEM NO.		MODEL NUMBER												
		GG75H	GG100H	GG125H	GG150H	GG175H	GG200H	GG225H	GG250H	GG275H	GG300	GG350H	GG375H	GG399H
1	Jacket Assembly	412613	412613	412613	412614	412614	412615	412615	412616	412616	412617	412618	412619	412619
2	Gas Manifold	410843	410843	410843	410844	410844	410845	410845	410846	410846	410847	410848	410848	410848
3	Main Burner Orifice (sea level):													
	Natural Gas	411880	411880	411880	411880	411880	411880	411880	411880	411880	411880	410518	411880	411945
	LP Propane Gas	410510	410510	410510	410510	410510	410510	410510	410510	410510	410510	—	410510	411729
4	Burner	410508	410508	410508	410508	410508	410508	410508	410508	410508	410508	410508	410508	410508
4A	Burner w/Bracket	410479	410479	410479	410479	410479	410479	410479	410479	410479	410479	410479	410479	410479
5	Burner Clip	410509	410509	410509	410509	410509	410509	410509	410509	410509	410509	410509	410509	410509
7A	Pilot Tube 1/4	410530	410530	410530	410530	410530	410530	410530	410530	410530	410530	410530	410530	410530
	Pilot Fitting 1/4	411768	411768	411768	411768	411768	411768	411768	411768	411768	411768	411768	411768	411768
7D	Access Door	410753	410753	410753	410754	410754	410755	410755	410756	410756	410757	410758	410758	410758
8	Base Assembly													
8A	With Insulation	412603	412603	412603	412604	412604	412605	412605	412606	412606	412607	412608	412608	412608
8B	Burner MTG Plate	410743	410743	410743	410744	410744	410745	410745	410746	410746	410747	410748	410748	410748
9	Heat Exchanger	412583	412583	412583	412584	412584	412585	412585	412586	412586	412587	412588	412588	412588
9a	Baffles (flat)	—	—	—	—	—	—	—	—	—	—	411901	—	—
10	Nipple	400225	400225	400225	400225	400225	400225	400225	400225	400225	400225	400225	400225	400225
11	Relief Valve	400103	400103	400103	400103	400103	400103	400103	400103	400103	400103	400103	400103	400103
12	Blank Plug	400238	400238	400238	400238	400238	400238	400238	400238	400238	400238	400238	400238	400238
13	Well for Hydrolevel Control w/LWCO	461012	461012	461012	461012	461012	461012	461012	461012	461012	461012	461012	461012	461012
13A	Hydrolevel Hydrostat Control Model #3200	461010	461010	461010	461010	461010	461010	461010	461010	461010	461010	461010	461010	461010
14	"J" Bolt	400148	400148	400148	400148	400148	400148	400148	400148	400148	400148	400148	400148	400148
15	Wing Nut	400147	400147	400147	400147	400147	400147	400147	400147	400147	400147	400147	400147	400147
16	Flue Collector	412636	412636	412636	412646	412646	412657	412657	412668	412668	412678	412679	412690	412690
17	Draft Hood	410891	410892	412468	410892	412499	410894	410894	410978	410978	410978	411815	411936	412670
18	Tridicator	910373061	910373061	910373061	910373061	910373061	910373061	910373061	910373061	910373061	910373061	910373061	910373061	910373061
19	Circulator	7902021	7902021	7902021	7902021	7902021	7902021	7902021	400115	400115	400115	400115	400115	400115
20	Circulator Nipple	400208	400208	400208	400208	400208	400208	400208	400208	400208	400208	400208	400208	400208
21	Tee	400203	400203	400203	400203	400203	400203	400203	400203	400203	400203	400203	400203	400203
22	Drain Cock	400201	400201	400201	400201	400201	400201	400201	400201	400201	400201	400201	400201	400201
23	Nipple	400202	400202	400202	400202	400202	400202	400202	400202	400202	400202	400202	400202	400202
24	Bushing													
25	Fiberglass Rope	403254	403254	403254	403254	403254	403254	403254	403254	403254	403254	403254	403254	403254
26	Blocked Vent Safety Switch Assembly	412058	412058	412058	412058	412058	412058	412058	412058	412058	412058	412058	412058	412057
26	Blocked Vent Safety Switch Assembly	—	—	—	—	—	—	—	—	—	411892*	411892*	411892*	411892*
27	Blocked Vent Safety Switch BX cable	412476	412476	412476	412476	412476	412476	412476	412476	412476	412476	412476	412476	412476
27	Blocked Vent Safety Switch Wire	—	—	—	—	—	—	—	—	—	411899*	411899*	411899*	411899*
28	Wire Support Bracket	—	—	—	—	—	—	—	—	—	—	411896	411896	411896
29	Anti-Short Bushing	411897	411897	411897	411897	411897	411897	411897	411897	411897	411897	411897	411897	411897
30	Rollout Safety Switch	411883	411883	411883	411883	411883	411883	411883	411883	411883	411883	411883	411883	411883
31	Rollout Switch Bracket	411894	411894	411894	411894	411894	411894	411894	411894	411894	411894	411895	411895	411895
32	Vent Damper	412705	412706	412706	412706	412706	412707	412707	412708	412708	412708†	412709†	412710†	412710†

NOTE: When ordering, please specify boiler model number, serial number and gas by name: "Natural" or "Propane". Refer to page 2 for exploded view of boiler. For intermittent ignition, see IID Parts List on page 3.


† Optional vent damper (GG-300 and larger) may be used with boilers equipped with IID only.

* For Modular Boilers Only

When ordering replacement parts, specify the boiler model number, serial number and gas by name (natural or propane). For replacement parts, heating contractors should contact their Slant/Fin boiler distributor.


Slant/Fin®

PUBLICATION NO. GG-11PL
Printed in U.S.A. 313
Part no. 41-2595




HONEYWELL IID CONTROLS


GALAXY - GG SERIES Intermittent Ignition (IID) Parts List



PILOT LIGHTER BOX
Mounts on jacket



GAS VALVE



Q345A
PILOT



IGNITION CABLE

HONEYWELL IID CONTROL SYSTEM	SLANT/FIN PART NO.	APPLICATION
Electric ignition pilot: Honeywell Q345A-1008 - natural gas Honeywell Q345A - propane gas	411612 411857	All natural gas boiler sizes All propane gas boiler sizes
Pilot orifice Natural gas only Propane gas only	410542 410524	All natural gas boiler sizes All propane gas boiler sizes
Gas valve - natural gas: Honeywell VR8204A, 1/2" x 3/4" Honeywell VR8304M, 1/2" x 3/4" Honeywell VR8304M, 3/4" x 3/4"	411864 411927 411929	GG-75 through GG-175 GG-200 through GG-325 GG-350H through GG-399H
Gas valve - L.P. propane gas Honeywell No. VR8304M, 1/2" x 3/4"	411928	All propane gas boiler sizes
Ignition model - natural gas Honeywell S8600F-1000 or Ignition model - natural gas Honeywell S8600M-3001 or Ignition model - natural gas UT 1003-621A	411873 412807 412101	All natural gas boiler sizes All natural gas boiler sizes All natural gas boiler sizes
Ignition model - L.P. propane gas Honeywell S8670E-1007 or Ignition model - L.P. propane gas Honeywell S8600M-1013 or Ignition model - L.P. propane gas Honeywell S8600H-3002 or Ignition model - L.P. propane gas UT 1003-624A	411947 411872 412808 412104	All propane gas boiler sizes All propane gas boiler sizes All propane gas boiler sizes All propane gas boiler sizes
Ignition cable w/ceramic boot	440153	All boiler sizes



SLANT/FIN CORPORATION, Greenvale, N.Y. 11548 • Phone: (516) 484-2600
FAX: (516) 484-5921 • Canada: Slant/Fin LTD/LTEE, Mississauga, Ontario

www.slantfin.com