



FEATURES

- Energy Savings of up to 86%
- Lumen Maintenance over 70% @ 50,000+ Hours
- No UV/IR Radiation, No Toxic Mercury
- Steel Trim in Brushed Nickel
- Die Formed of 22 Gauge Plated Steel
- Replaces 3 x 100W Incandescent

OPTICS

- White Acrylic Diffuser

APPLICATIONS

- Ceiling Installations for General Ambient Lighting in Homes, Apartments, and Offices
- Hotels, Hospitality Areas
- Corridors, Lobbies, Stairways

CERTIFICATIONS

- ETL Listed
- Energy Star

SPECIFICATIONS

Part Number: 3200LEDB-35

Manufacturer Limited Warranty: 3 Years

Kelvin Temperature (CCT): 3000K

Wattage: 42W

Lumens: 3000 lm

Efficacy: 71.4 lm/w

CRI: 82

Dimmable: No

Input Voltage: DC 120V

Certifications: UL Listed

DLC Listed: No

Average Hour Life: 50,000 hrs

Max. Ambient Temperature: 104 ° F

Min. Ambient Temperature: -4 ° F

Power Factor: >0.9

THD: <20%

TECHNICAL

Weight: 11.1 lbs

Length: 32.5"

Product Height: 4.625"

Product Width: 18.125"

LED Beam Angel: 120

LED Type: Integrated LED Array





LINE DRAWINGS

