

## PF1200 Series

# Two-Piece Toilet Vitreous China



### Product Features

- Two-piece vitreous china, available 10", 12", 14" RI
- Stylish tank design
- Gravity fed (1.6gpf/6.0Lpf)
- Box rim with integral jets
- 2" glazed trapway
- 8" x 9" water surface
- Close coupled tank with cover
- Anti-siphon ballcock prevents back-siphoning
- Sanitary bar on all bowls
- Quick connect, 2 bolt tank to bowl installation
- Color matched trip lever
- Available with Fluidmaster upgrade
- Available with RH trip lever
- Available with insulated tank
- Available round front, elongated and ADA
- Seat and supply not included



PF1203WH / PF3112WH

### Codes and Standards

- ADA
- IAPMO/UPC
- ASME A112.19.2
- CSA B45.0
- CSA B45.1

### Technical Information

Fixture is ADA compliant.	<b>ADA</b>
<b>Fixture:</b>	
Configuration	two-piece toilet
Water per flush	1.6 gpf/6.0 lpf
Spud size	N/A
Passageway	2" glazed
Water area	8" X 9"
Water depth from rim	6 1/2"
Seat post hole centers	5 1/2"

### Specified Model

Model	Model Description	Color Finishes
* PF1200	Bowl only box rim RF	○ White    ○ Biscuit    ○ Bone
* PF1201	Bowl only box rim EB	○ White    ○ Biscuit    ○ Bone
PF1203	Bowl only box rim ADA	○ White    ○ Biscuit    ○ Bone
PF3112	Tank only 12" RI for 1200 series	○ White    ○ Biscuit    ○ Bone
PF3312	Tank with Fluidmaster 400A, for 12" RI	○ White    ○ Biscuit
PF3110	Tank only 10" RI for 1200 series	○ White
PF3114	Tank only 14" RI for 1200 series	○ White
PF140934PK	Ballcock assy F/PF 3112 tank	

add "R" to tank for RH tank lever (3112 only)  
add "U" to tank for insulated tank (3112 only)

\* = complies with CSA B651

= complies with ADA & CSA B651



