


## **Exposed Z6017 Model**

## for Service Sinks



## **Flow Options**

□ WS1
□ WS
□ Standard Flush
1.6 Gallons Per Flush
3.5 Gallons Per Flush
6.5 Gallons Per Flush

## **Suffix Options (Check/Specify Appropriate Options)**

		` ' ' ' ' ' ' ' ' ' ' ' ' ' ' ' ' ' ' '
E	3G	BioCare ADA Handle
+	1	Handle on Front of Flush Valve
L	_	1" [25] Metal Push Button
L	_3	3" [76] Metal Push Button
	/C	Vandal Resistant Stop Cover
-)	/B	Sweat Solder Kit
-\	C)	Cast Wall Flange
-\	/H	One Wall Bumper
-)	/J	Split Ring Pipe Support
-\	/K	Solid Ring Pipe Support

Other

**ENGINEERING SPECIFICATION: ZURN Z6017 Aquaflush Exposed Clinic Service Sink Flush Valve -** Exposed, quiet diaphragm-type, chrome plated flushometer valve with a polished exterior. Complete with a chloramine resistant, dual seal diaphragm with a clog resistant by-pass. The valve is ADA compliant with a non-hold-open and no leak handle feature, high back pressure vacuum breaker, one piece hex coupling nut, adjustable tailpiece, spud coupling and flange for top spud connection. Control stop has internal siphon-guard protection. Internal seals are made of chloramine resistant materials.

☐ Z6017PL- Aquaflush Plus is furnished as specified above and includes sweat solder kit, vandal resistant stop cap, and cast wall flange.

This space is for Architectural/engineering Approval

Product No. Z6017

ZURN INDUSTRIES, LLC. ♦ COMMERCIAL BRASS OPERATION ♦ 5900 ELWIN BUCHANAN DRIVE ♦ SANFORD NC 27330
Phone: 1-800-997-3876 ♦ Fax: 919-775-3541 ♦ World Wide Web: www.zurn.com
In Canada: ZURN INDUSTRIES LIMITED ♦ 3544 Nashua Drive ♦ Mississauga, Ontario L4V1L2 ♦ Phone: 905-405-8272 Fax: 905-405-1292

Dwg. No. 56638