

PFXCHFU18

Stainless Steel Flexible Water Heater Connectors




Specification:


CSST: Stainless Steel 304 (ASTM A240)
Fittings: Chrome-Plated Brass 3771
Gasket: High Quality EPDM
Working Pressure: Up to 125 psig
For use with CPVC and PEX, and copper (types L, M, K)

Intermittent Impulse Pressure: Up to 180 psig
Temperature: -40°F to 180°F (82°C)
Minimum Bend Radius: 2.5"
100% Leak Tested

Installation Instructions:



1. Make a clean cut onto the copper, CPVC, or PEX tubing. Deburr the edges to ensure that the outside diameter is free of sharp ridges.



2. Verify that all the inner components are placed in order.
A. Grab Ring
B. Spacer
C. O -Ring



3. Measure out 1.2" and mark the tubing.



4. Insert the pipe into the fitting up to the 1.2" mark. Pull on the pipe to make sure that it is secure. Test the system for leakage before use.